



Pushing Performance
Since 1945

Ha-VIS eCon 2080GBT-A



Image is for illustration purposes only. Please refer to product description.

Part number	24 02 408 0000
Specification	Ha-VIS eCon 2080GBT-A
HARTING eCatalogue	https://harting.com/24024080000

Identification

Series	Ha-VIS eCon 2000
Element	Industrial Ethernet Switches
Specification	Unmanaged
Type of Ethernet	Full Gigabit Ethernet

Version

Total number of ports	8
Fixing	35 mm DIN rail acc. to EN 60715
Switching technology	Store and Forward
Frame size	9.216 kB
MAC table size	4k Entries
Packet buffer size	1.5 Megabit
Non blocking	Yes
Quality of service	Yes
Energie Efficient Ethernet	Yes
Flow control	Off
Signal contact	No
PoE functionality	No
Jumbo frame support	Yes
Pack contents	Pluggable screw contact for power supply Assembly instructions



Pushing Performance
Since 1945

Termination data

Nominal voltage	24 V DC
	48 V DC
Permissible voltage	9 ... 60 V DC
Surge protection	Yes
Operating current	<130 mA @ 24 V DC
	<68 mA @ 48 V DC
Supply circuit	SELV (Circuit Breaker 10 A)
Starting current	<1.4 A @ 24 V DC
	<2.3 A @ 48 V DC
Overcurrent protection	2 A at input
Power consumption	<3.12 W @ 24 V DC
Termination method	Pluggable screw contact
Number of contacts	3
Conductor cross-section	0.08 ... 2.5 mm ²
Conductor cross-section (AWG)	AWG 28 ... AWG 12
Pinout	+ / - / FE
Reverse polarity protection	Yes

Technical characteristics

Pollution degree	2
Overvoltage category	II
Operating temperature	-40 ... +70 °C
Storage temperature	-40 ... +85 °C
Relative humidity	0 ... 95 % Non-condensing (operation)
	0 ... 95 % Non-condensing (storage/transport)
Air pressure	≥795 hPa ≈ 2000 m
Degree of protection acc. to IEC 60529	IP30 mated condition
MTBF	≈1,015,000 h

Ethernet ports copper

10/100/1000 Mbit/s (RJ45-Ports)	8
Transmission standard	10BASE-Te
	100BASE-TX EEE
	1000BASE-T EEE
Auto-negotiation	Yes
Auto-polarity	Yes



Pushing Performance
Since 1945

Ethernet ports copper

Auto-MDI(X)	Yes
Transmission physics	Twisted Pair Cat. 5
Data rate	10 Mbit/s
	100 Mbit/s
	1,000 Mbit/s
Transmission length	100 m

Material properties

Material (hood/housing)	Aluminium (anodised)
Length	27.3 mm
Width	60 mm
Height	113.5 mm
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	bbcc04b5-5176-4454-afbc-a635daae5e7b
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Specifications	EN 55022 Radio disturbance characteristics
	EN 61000-4-2 Electrostatic discharge (ESD)
	EN 61000-4-3 Electromagnetic field
	EN 61000-4-4 Rapid transients (burst)
	EN 61000-4-5 Surge voltages
	EN 61000-4-6 conducted disturbances
	EN 61000-6-4 emission standard
	IEC 60068-2-6 Vibration (sinusoidal)
UL / CSA	UL 61010 NRAQ.E253944
	CSA-C22.2 No. 61010 NRAQ7.E253944
Approvals	CE
	on request



Pushing Performance
Since 1945

Specifications and approvals

FCC	Yes
-----	-----

Commercial data

Packaging size	1
Net weight	290 g
Country of origin	Germany
European customs tariff number	85176200
GTIN	5713140329546
eCl@ss	19170130 Network switch (general application)
ETIM	EC000734
UNSPSC 24.0	43222612