
NOTES:

1. MATERIALS & FINISH:
   1.1 HOUSING & COUPLING NUT: PASSIVATED STAINLESS STEEL
   1.2 DIELECTRIC: PTFE (TEFLON)
   1.3 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
   1.4 GASKET: SILICONE RUBBER

2. SPECIFICATIONS:
   2.1 FREQUENCY RANGE: DC to 18 GHz
   2.2 INPUT POWER (MAX): 0.5 WATTS AT +25°
       DERATED LINEARLY TO 0 WATTS AT +125°
   2.3 VSWR (MAX): 1.10+0.01f(GHz)
   2.4 IMPEDANCE: 50 OHMS NOMINAL
   2.5 OPERATING TEMPERATURE RANGE: −55°C to +125°C



MODEL NUMBER
TRM−2180−M0−SSM−02

REV.	DESCRIPTION	DATE
−	RELEASED	12/2/94
A	ECN 14280	2/10/95
B	ECN 18498	4/26/02
C	ECN 21477	8/24/07
D	ECO 22376	3/8/10
E	ECO 57918	6/8/21

NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
3 PLACE DECIMALS ±.005
2 PLACE DECIMALS ±.02
FRACTIONS ±1/64
PARALLELITY: T.I.R. _____
FLATNESS: T.I.R. _____
CONCENTRICITY: T.I.R. _____
ANGLES AND PERPENDICULARITY: ±1°

CAGE CODE 34078

MIDWEST MICROWAVE

cinch CONNECTIVITY SOLUTIONS a bel group

TITLE
TERMINATION
SSMA MALE

DRAWN/DATE	ENG./DATE	DRAWING NUMBER	REV.
M.HOLLMAN 12/2/94	A.OSGA 12/2/94	TRM−2180−M0−SSM−02−01	E
CHECKED/DATE	APPROVED/DATE		
A.BEATTY 12/2/94	C.RIGGE 4/26/02		

SCALE: 4:1 SHEET 1 of 1

Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.