



# Customer Information Sheet

| DRAWING No.: M80-263F2XX-XX-XX | IF IN DOUBT - ASK | © | NOT TO SCALE | THIRD ANGLE PROJECTION | ALL DIMENSIONS IN mm |
|---|---|---|---|---|---|




NOTES:
1. CONNECTORS ARE SUPPLIED WITHOUT CONTACTS.
2. SUITABLE FOR FEMALE CABLE POWER, COAXIAL AND SIGNAL DATAMATE CONTACTS - FOR MORE INFORMATION PLEASE VISIT HARWIN.COM.
3. FOR MECHANICAL AND ELECTRICAL SPECIFICATION SEE COMPONENT SPECIFICATION C005XX (LATEST ISSUE).

| DIMENSION | CALCULATIONS |
|---|---|
| DIM 'A' | ((4 x No. OF SPECIAL CONTACTS) + No. OF SIGNAL CONTACTS) + 10.0 |
| DIM 'B' | ((4 x No. OF SPECIAL CONTACTS) + No. OF SIGNAL CONTACTS) + 5.0 |

EXAMPLES: CONNECTOR WITH 02 **RIGHT** (BEFORE No.1) SPECIAL CONTACTS,
04 SIGNAL CONTACTS AND 02 **LEFT** (AFTER No.1) SPECIAL CONTACTS,
**M80-263F202-04-02**
DIM 'A' = 30.00mm, DIM 'B' = 25.00mm

CONNECTOR WITH NO SIGNAL CONTACTS,
AND 06 SPECIAL CONTACTS,
**M80-263F206-00-00**
DIM 'A' = 34.00mm, DIM 'B' = 29.00mm

## ORDER CODE:

**M80-263F2XX-XX-XX**

- TOTAL No. OF SPECIAL CONTACTS BEFORE No.1 **(RIGHT)**: 00 TO 12
- TOTAL No. OF SIGNAL CONTACTS: 00 TO 50 (EVEN NUMBERS ONLY)
- TOTAL No. OF SPECIAL CONTACTS AFTER No.1 **(LEFT)**: 00 TO 12

SINGLE SPECIAL CONTACT HAS EQUIVALENT FOOTPRINT OF 4 SIGNAL CONTACTS.
EACH MOULDING CAN HOUSE A MAXIMUM OF 50 SIGNAL CONTACTS PROVIDING THERE ARE NO SPECIAL CONTACTS, OR 12 SPECIAL CONTACTS PROVIDING THERE ARE NO SIGNAL CONTACTS, AND ALL CONFIGURATIONS BETWEEN.

IF THERE ARE NO SIGNAL CONTACTS, USE ONLY THE FIRST SPECIAL CONTACT QTY
I.E. M80-263F2XX-00-00

| RA | 2 | 21.08.20 | 30137 |
|---|---|---|---|
| NAME | ISS. | DATE | CN/CO |
| APPROVED: | R.ALEXANDER | | |
| CHECKED: | R.PORTLOCK | | |
| DRAWN: | R.PORTLOCK | | |
| CUSTOMER REF.: | | | |
| ASSEMBLY DRG: | | | |

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.20mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL: SEE ABOVE
FINISH: SEE ABOVE
S/AREA: - mm²

TITLE: JACKSCREW DATAMATE MIXED TECHNOLOGY FEMALE CRIMP MOULDING WITH HARDWARE
DRAWING NUMBER: M80-263F2XX-XX-XX
SHT 2 OF 2