



Part Number : [1202480027](#)
Product Description : MPIS Micro-Change (M12)
Passive Junction Box, Top-Mount, 8 Ports, LED for NPN
Sensor, WSOR Cable, 15.0m Length
Series Number : 120248
Status : Active
Product Category : Passive Distribution Boxes
Engineering Number : BTB800N-FBW-15



Documents & Resources

Drawings

[1202480027_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	120248
Description	MPIS Micro-Change (M12) Passive Junction Box, Top-Mount, 8 Ports, LED for NPN Sensor, WSOR Cable, 15.0m Length
IP Rating	IP67
Product Name	MPIS
UPC	889056329736

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	NPN
Voltage - Maximum	10-30V DC
Wiring Configuration	Single I/O per Port

Physical

Bus I/O	N/A
Cable Connector Orientation	Straight
Cable Length	15.0m
Home Run Cable Length	15.0m
Home Run Connector	N/A
Home Run Interface	Pigtail

Keyway	A-Coded
LED Indicator	NPN Sensors
Material - Cable Jacket	TPU
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	1754.394/g
Orientation	Top-Mount
Poles	4
Poles (wired)	4
Ports	8
Temperature Range - Operating	-25°C to +85°C
Wire/Cable Type	WSOR

This document was generated on Sep 23, 2025