

SP1333 Series

8pF 30kV Bidirectional Discrete TVS

HF RoHS Pb GREEN




Web Resources




Download ECAD models, order samples, and find technical resources at www.littelfuse.com

Pinout



Functional Block Diagram



Description

The SP1333 back-to-back diodes are fabricated in a proprietary silicon avalanche technology. These diodes provide a high ESD (electrostatic discharge) protection level for electronic equipment. The SP1333 TVS can safely absorb repetitive ESD strikes above the maximum contact discharge level specified in the IEC 61000-4-2 international standard (Level 4, $\pm 8\text{kV}$ contact discharge) without performance degradation. The back-to-back configuration provides symmetrical ESD protection for data lines. Additionally, the SP1333 offers up to 5A 8/20 surge rating with low clamping voltages.


Features and Benefits

- ESD, IEC 61000-4-2, $\pm 30\text{kV}$ contact, $\pm 30\text{kV}$ air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Lightning, 5A (8/20 μs as defined in IEC 61000-4-5 2nd edition)
- Low capacitance of 8pF (TYP @ $V_R=0\text{V}$)
- Low leakage current of 1nA (TYP) at 3.3V
- Space efficient 0201
- Halogen free, Lead free and RoHS compliant
- Moisture Sensitivity Level (MSL -1)
- AEC-Q101 qualified

Applications

- Mobile Phones
- Smart Phones
- Portable Medical
- MP3/PMP
- Portable Navigation Components
- Tablets
- Small Size Panel
- Point of Sale Terminals

Application Example



Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

SP1333 Series

8pF 30kV Bidirectional Discrete TVS

Absolute Maximum Ratings

Symbol	Parameter	Value	Units
I_{PP}	Peak Current ($t_p=8/20\mu s$)	5	A
T_{OP}	Operating Temperature	-40 to 125	°C
T_{STOR}	Storage Temperature	-55 to 150	°C

Caution: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Electrical Characteristics ($T_{OP}=25^\circ C$)


Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R=1\mu A$			3.3	V
Breakdown Voltage	V_{BR}	$I_R=1mA$	3.5	4.5		V
Reverse Leakage Current	I_{LEAK}	$V_R=3.3V$		1	50	nA
Clamp Voltage ¹	V_C	$I_{PP}=1A, t_p=8/20\mu s, I/O$ to I/O		5	7	V
		$I_{PP}=5A, t_p=8/20\mu s, I/O$ to I/O		7.5	9	V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p=100ns, I/O$ to I/O		0.3		Ω
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 30			kV
		IEC 61000-4-2 (Air Discharge)	± 30			kV
Diode Capacitance ¹	$C_{I/O-I/O}$	Reverse Bias=0V		8	10	pF

Note:


1. Parameter is guaranteed by design and/or component characterization.

2. Transmission Line Pulse (TLP) with 100ns width, 2ns rise time, and average window $t_1=70ns$ to $t_2=90ns$

Capacitance vs. Reverse Bias




8/20 μs Pulse Waveform




SP1333 Series

8pF 30kV Bidirectional Discrete TVS


Negative Transmission Line Pulsing (TLP) Plot




Positive Transmission Line Pulsing (TLP) Plot




IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage



IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage



Clamping voltage vs. IPP for 8/20μs waveshape




SP1333 Series

8pF 30kV Bidirectional Discrete TVS

Soldering Parameters

Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 120 secs
Average ramp up rate (Liquidus) Temp (T_L) to peak		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Temperature (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/-5} °C
Time within 5°C of actual peak Temperature (t_p)		30 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		260°C




Ordering Information

Part Number	Package	Min. Order Qty.
SP1333-01UTG	0201 DFN	15,000


Product Characteristics

Lead Plating	Pre-Plated Frame
Lead material	Copper Alloy
Substrate Material	Silicon
Body Material	Molded Compound
Flammability	UL Recognized compound meeting flammability rating V-0

Part Marking System




Part Numbering System



SP1333 Series


8pF 30kV Bidirectional Discrete TVS

Package Dimensions — 0201 DFN



Symbol	0201 DFN					
	Millimeters			Inches		
	Min	Typ	Max	Min	Typ	Max
A	0.30	0.31	0.32	0.012	0.012	0.013
A1	0.00	0.02	0.05	0.000	0.001	0.020
b	0.18	0.23	0.28	0.007	0.009	0.011
L1	0.12	0.17	0.22	0.005	0.007	0.009
L2	0.13	0.18	0.23	0.005	0.007	0.009
D	0.55	0.60	0.65	0.022	0.024	0.026
E	0.25	0.30	0.35	0.010	0.012	0.014
e	0.35 BSC			0.014 BSC		

Embossed Carrier Tape & Reel Specification — 0201 DFN



Symbol	Millimeters		Inches	
	Min	Max	Min	Max
A0	0.33	0.40	0.013	0.016
B0	0.63	0.70	0.025	0.028
D0	1.40	1.60	0.055	0.063
E	1.65	1.85	0.065	0.073
F	3.45	3.55	0.136	0.140
K0	0.30	0.39	0.012	0.015
P0	1.90	2.10	0.075	0.083
P1	1.95	2.05	0.077	0.081
P2	3.90	4.10	0.154	0.161
T	0.13	0.25	0.005	0.010
W	7.90	8.30	0.311	0.327

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.