

HS LCA-WH 10X3-L - Signal light

1474406

<https://www.phoenixcontact.com/us/products/1474406>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Signal light with litz wires, active, flexible, Raised head, emission surface: spherical, number of displays: 1, (1 row, 1 column), diameter: 10 mm



Commercial data

Item number	1474406
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGABC
GTIN	4063151887957
Weight per piece (including packing)	5.9 g
Weight per piece (excluding packing)	5.86 g
Customs tariff number	90019000
Country of origin	TN

HS LCA-WH 10X3-L - Signal light

1474406

<https://www.phoenixcontact.com/us/products/1474406>



Technical data

Notes

Assembly note	The light guide is designed to be pressed into an H7-tolerated receptacle. Dry-install the LED display by pressing it in vertically. As an alternative, you can glue in the LED display, e.g., using LOCTITE 460.
General	Please observe the application note in the download area.

Product properties

Product type	Light
Number of positions	1
Alignment	flexible
Type	active, flexible
Conductor type	Signal light with litz wires
Head form	Raised head
Number of indicators	1 (1 row x 1 column)

Dimensions

Diameter	10 mm (Aperture diameter)
	3 mm (Lens diameter)
Hole diameter	8 mm ^{H7}
Dimensions	94 mm (Cable ends)

Material specifications

Insulating material	PC
---------------------	----

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP68
Ambient temperature (operation)	-20 °C ... 80 °C

Packaging specifications

Type of packaging	PE bag
-------------------	--------

HS LCA-WH 10X3-L - Signal light

1474406

<https://www.phoenixcontact.com/us/products/1474406>



Classifications

ECLASS

ECLASS-11.0	27110201
ECLASS-12.0	27110201
ECLASS-13.0	27110201

ETIM

ETIM 9.0	EC002750
----------	----------

HS LCA-WH 10X3-L - Signal light

1474406

<https://www.phoenixcontact.com/us/products/1474406>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com