

SERIES

NO.OF CONTACTS

09,15,25,37

TYPE OF CONTACTS

P-PIN

TYPE OF TERMINATION

33-ANGLED SPILL

PITCH 2.84 USA

FOOT PRINT 8.08 USA

HEIGHT OF TERMINATION

E-2.00mm COMPATIBLE FOR 1.6mm PCB

RoHS INFORMATIONS

"This LF product meets European Union Directives and other country regulations as described in GS-22-008"

The housing will withstand exposure to 260°C peak temperature for 30 seconds in a convection,infra-red or vapor reflow oven solder application.

Packaging as per GS-14-920

PRODUCT SPECIFICATION

See :- GS-12-433

PACKAGING SPECIFICATION

See :- GS-14-1139

SEE NOTE RoHS

PACKAGING SPECIFICATION

12- TAPE & REEL PACKAGING

MOUNTING OPTIONS




RV->LIF METAL PEG+F.SCREW LOCK UNC 4 40+METAL BRACKET

RL->LIF METAL PEG+ INSERT M3+METAL BRACKET

RX->LIF METAL PEG+ INSERT UNC 4-40 +METAL BRACKET

PLATING

6-500 Mating/Un-mating performance

mat'l. code SEE.TECH.SPEC				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DELTA-D												
ltr	ecn no		dr	date		tolerances unless otherwise specified				title DELTA-D A/S MALE PIP CONNECTOR US VERSION												
A	I07-0167		AS	2007-12-04		angles	linear															
B	I08-0175		AS	2009-01-14				.00±0.1														
C	I09-0162		AS	2009-08-17		0°±1°		.000±.00X		scale —												
						dr	ANISH.SALAM		2007-12-04				dwg no				sheet 1 of 2				size	
						engr	ANISH.SALAM		2009-08-17				C-DD-0101						A3			
						chr	ANISH.SALAM		2009-08-17													
						appd	ANISH.SALAM		2009-08-17													
sheet index		revision sheet		C	C																	
				1	2																	

