Ratings
Voltage: 300 V
Temperature: -40~105 °C
Flammability: VW-1

Conductor
Conductor count: 10
Gauge: 24 AWG 0.2 mm²
Material: tinned copper strands
Strand size: ∅0.1 x 26
Resistance at 20 °C: 94.2 Ω /km max


Insulator
Material: FEP
Color: red, black, white, yellow, blue, green, orange, purple, gray, brown
Diameter: ∅0.92 ±0.10
Nominal thickness: 0.13 mm
Resistance at 20 °C: 10 MΩ /km min


Filler
Material: aramid fiber

Wrap
Material: cotton paper

Outer jacket
Material: TPE
Color: black
Diameter: ∅5.2 ±0.25
Nominal thickness: 0.6 mm

Wire marking: E339579 UL AWM STYLE 21296 24 AWG 105°C 300V VW-1 - - - cUL AWM I A 105°C 300V FT1 TENSILITY DGT





Revision:	Date:	Description:
A	4/28/2021	Initial release

Prepared: AW Digitally signed by AW Date: 2021.04.28 17:15:56 -07'00'

Verified: JC Digitally signed by JC Date: 2021.05.05 11:36:31 -07'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:
RoHS compliant
Phthalate free
Function test: no open, no short circuit, no intermittent

Description:
Wire, 10C TS, 24 AWG, UL 21296, 300V, 105C, 5.2 mm, TPE

TENSILITY
tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com

Size: A
Part number: 30-01967
Scale: 10:1
Sheet 1 of 1

To see a custom version of this cable assembly, call Tensility at 541-323-3228 or email engineering@tensility.com

5 4 3 2 1

Downloaded from Arrow.com.