

TPB11FGVRA004 Product Details



TPB11FGVRA004

TE Internal Number: 1-1825097-6

Active

Pushbutton Switches

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Switch
- Tactile
- Single Pole - Double Throw Configuration (Pole-Throw)
- Contact Rating = 0.4VA
- Operating Function = On [On]

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Add to My Part List

Request Sample

Find Similar Products

Buy Product

Documentation & Additional Information	
Product Drawings: • PUSHBUTTON SWITCH, TPB SERIES (PDF, English) Catalog Pages/Data Sheets: • SWITCHES_CORE_PROGRAM_CATALOG (PDF, English) Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available List all Documents	Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Product Type = Switch • Tactile = Yes • Configuration (Pole-Throw) = Single Pole - Double Throw • Series = TPB • Mount Angle = Vertical Right Angle • Termination Type = Printed Circuit • Actuator Style = Round Electrical Characteristics: • Contact Rating = 0.4VA Body Features: • Mount Style = Through-Hole • Actuator Length (mm [in]) = 4.50 [0.117] • Actuator Profile = Extended • Actuator Color = Black • Case Material = Thermoplastic (LCP) • Actuator Material = Nylon	Configuration Features: • Operating Function = On [On] • Ganged = No • ESD Grounding Terminal = Without • Actuator Force (g [oz]) = 50.00 – 400.00 [1.770 – 14.120] • Number of Actuators = Single • Illuminated = No • Dust Proof = No • Support Bracket = Without • Snap Action = Without Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: • Temperature Rating = Standard

Contact Features:

- Contact Plating = Gold
- Contact Base Material = Copper Alloy

Housing Features:

- Process Sealed = No
- Low Profile = No

Packaging Features:

- Packaging Method = Loose Piece

Other:

- Brand = Alcoswitch

Corporate Information

- Who We Are
- Investors
- News Room
- Supplier Portal
- Careers

Quick Links

- Check Distributor Inventory
- Cross Reference
- Find Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Search Knowledge Base
- Manage your Account

Keep Me Informed

Receive TE News, Events & Technology Updates

>

