






- NOTES
- 1 - INPUT MEDIA:
 - P1 - DRY GASES ONLY: CONNECTION SIDE OF SENSOR
 - P2 - LIMITED ONLY TO THOSE MEDIA THAT WILL NOT ATTACK POLYESTER, SILICON OR SILICONE BASED ADHESIVE
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - LIMIT SOLDERING TO 315°C MAX FOR 10 SECONDS MAX
 - 4 - UNITS ARE OF PLASTIC CONSTRUCTION
 - 5 - SPAN = 55"H₂O
 - 6 - PRESSURE TRANSDUCER IS USED IN P1 < P2 CONFIGURATION

GENERAL OPERATING CHARACTERISTICS

PRESSURE RANGE	-39 TO 55" H ₂ O
OVERPRESSURE	1035 mmHg (20 PSI)
TEMPERATURE RANGES	
STORAGE	-55°C TO +125°C
OPERATING	-40°C TO +85°C
COMPENSATED	0°C TO +65°C
SUPPLY VOLTAGE	7 TO 16 Vdc
SUPPLY CURRENT	20mA MAX WITH 10K LOAD
OUTPUT VOLTAGE	PROPORTIONAL TO SUPPLY VOLTAGE OVER ABOVE RECOMMENDED RANGE
SHORT CIRCUIT LIMIT	MAY BE SHORTED INDEFINITELY
OUTPUT RIPPLE	NONE
GROUND REFERENCE	SUPPLY AND OUTPUT ARE COMMON
RATIOMETRICITY ERROR	
7V TO 8V OR 8V TO 9V	±.5% SPAN (TYP)
9V TO 12V	±2.00% SPAN (TYP)
STABILITY OVER 1 YEAR	±.50% SPAN (TYP)

ELECTRICAL PERFORMANCE AT 25°C AND 10.00±.01 Vdc SUPPLY

OUTPUT VOLTAGE	
MINIMUM SCALE (-39" H ₂ O)	1.0275±.0950 Vdc (TYP)
NULL (0" H ₂ O)	3.916±.070 Vdc
FULL SCALE (55" H ₂ O)	7.991±.070 Vdc (TYP)
SPAN (0 TO 55" H ₂ O)	4.075±.070 Vdc
SENSITIVITY	74.08±2.54 mV/"H ₂ O (TYP)
LINEARITY (0 TO 55"H ₂ O)	.625% SPAN MAX
(-39 TO 0"H ₂ O)	.625% SPAN MAX
TEMPERATURE ERROR OVER 0 TO +65°C	
NULL SHIFT	1.0% SPAN MAX
SPAN SHIFT	1.0% SPAN MAX
COMBINED SHIFT	2.0% SPAN MAX
HYSTERESIS & REPEATABILITY	.25% SPAN (TYP)



TYPE "D" (DIFFERENTIAL)

METRIC	INCH
0.4	.016
0.25	.010
0.51	.020
1.0	.039
1.5	.04
2.5	.099
3.52	.139
5.00	.197
5.08	.200
6.1	.240
7.1	.280
10.0	.39
12.3	.484
12.6	.496
16.2	.64
17.9	.70
18.5	.73
30.0	1.18
52.40	2.06
59.8	2.35

THIRD ANGLE PROJECTION		
SCALE 2 : 1		
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
NO PLACE	(0)	± 1 mm
ONE PLACE	(0.0)	± 0.4 mm
TWO PLACE	(0.00)	± 0.15 mm
ANGLES		±
WEIGHT	31 GRAMS	

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		
MICRO SWITCH a Honeywell Division FED. WFG. CODE 91929	PRESSURE TRANSDUCER	CATALOG LISTING
		142PC05D97