

Representative Image

Catalog No. L-7-50-0-M

Description: CABLE TIE 50LB 7IN UV BLK 1-PC BULK

UPC No 728494917108

Home > Wire & Cable Management > Catamount > Cable ties

Standard Cable Tie, Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Black Color Nylon 6.6, Length of 192mm (7.6 Inches) for Bundle Diameter up to 47.6mm (1.87 Inches), Width of 4.6mm (0.18 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Operating Temperature of -40 Degrees Celsius (-40 F) to 85 Degrees Celsius (185 F), Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, 1000 Pack

Descriptors

Category	Cable ties
Type	UV Resistant Black
Application	Cable ties are primarily used to cinch wires and cables together to form a neat and organized bundle

Specifications

Material	Natural Polyamide (Nylon 6.6)
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	50 lb, 222 N

Classifications

Brand Name	Catamount
Standard	UL E49405

Dimensions

Width	0.18 in, 4.6 mm
Length	7.48 in, 190 mm
Thickness	0.05 in, 1.3 mm
Bundle Diameter	0.12 in - 1.81 in, 3 mm - 46 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

Downloaded from Arrow.com.

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.