NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL AND FINISH:
   1.1 BODY & COUPLING NUT: GOLD PLATED BRASS
   1.2 CONTACT: GOLD PLATED BERYLLIUM COPPER
   1.3 INSULATOR: PTFE (TEFLON)
   1.4 COUPLING SPRING: BERYLLIUM COPPER UNPLATED

2. ELECTRICAL SPECIFICATIONS:
   2.1 IMPEDANCE: 50 OHMS
   2.2 FREQUENCY: 0 - 26.5 GHz
   2.3 VSWR: 1.05+.02F(GHz) MAX AT 0-18 GHz, <1.50 TYPICAL AT 18-26.5 GHz
   2.4 WORKING VOLTAGE: 170 VRMS MAX AT SEA LEVEL
   2.5 DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS MIN AT SEA LEVEL
   2.6 INSULATION RESISTANCE: 1000 MEGOHMS MIN
   2.7 CONTACT RESISTANCE:
   CENTER CONTACT: INTIAL 3.0 MILLIOHM MAX,
   AFTER ENVIRONMENTAL 4.0 MILLIOHM MAX
   OUTER CONDUCTOR: INITIAL 2.0 MILLIOHM MAX,
   AFTER ENVIRONMENTAL - N/A
   2.8 CORONA LEVEL: 125 VOLTS MIN AT 70,000 FEET
   2.9 RF HIGH POTENTIAL WITHSTANDING VOLTAGE: 335 VRMS AT 4 & 7 MHz

3. MECHANICAL SPECIFICATIONS:
   3.1 ENGAGE/DISENGAGE TORQUE: 2 INCH-POUNDS MAX
   3.2 MATING TORQUE: 7-10 INCH-POUNS WHEN BODY SUPPORTED WITH WRENCH
   8* INCH POUNDS MAX UNSUPPORTED
   3.3 CONTACT RETENTION FORCE: 6 LBS MIN AXIAL FORCE ON MATING END
   4 IN-OZ MIN RADIAL TORQUE
   3.4 DURABILITY: 500 CYCLES MIN


4. ENVIRONMENTAL:
   (MEETS OR EXCEEDS THE APPLICABLE PARAGRAPH OF MIL-PRF-39012)
   4.1 THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B,
   EXCEPT 115°C HIGH TEMP
   4.2 OPERATING TEMPERATURE: -65°C TO 165°C
   4.3 CORROSION: MIL-STD-202, METHOD 101, CONDITION B
   4.4 SHOCK: MIL-STD-202, METHOD 213, CONDITION I
   4.5 VIBERATION: MIL-STD-202, METHOD 204, CONDITION D
   4.6 MOISTURE RESISTANCE: MIL-STD-202, METHOD 106


5. ALL HOLES PLATED THRU ENTIRE CIRCUIT BOARD STACKUP.


6. HOLE PATTERNS SYMMETRICAL ABOUT CENTER CPW TRACE.

7. FOR OPTIMUM CIRCUIT BOARD HIGH FREQUENCY PERFORMANCE:
   7.1 MAINTAIN SOLID GROUND PLANE BELOW HF SUBSTRATE.
   7.2 CONTROL PULLBACK OF TRACE AND GROUND FROM BOARD EDGE.
   7.3 CONTINUE GROUNDED COPLANAR LINE BEYOND GROUND PADS.
   7.4 PLACE 16 MIL DIA GROUND VIAS ON BOTH SIDE OF COPLANAR
   WAVEGUIDE LINE AT 50 MIL INTERVALS ALONG ENTIRE LENGTH.
   7.5 IMMERSION GOLD PLATE (ENIG) ALL CONDUCTORS PER IPC-4552.


8. REFERENCE DIMENSIONS FOR 50 OHM GROUNDED CPW LINE, USING
   ROGERS R04003, 8 MIL HIGH FREQUENCY CIRCUIT BOARD SUBSTRATE:
   TRACE WIDTH: 15.5 MILS
   GROUND GAPS: 10 MILS
   CONDUCTOR THICKNESS: 1.4 MIL (INCLUDES PLATING)







MOUNTING FOOTPRINT
(TOP VIEW, INCLUDING TRACE DIMENSIONS)



cinch CONNECTIVITY SOLUTIONS a bel group	3RD ANGLE PROJECTION	JOHNSON
This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature and must be kept and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	RoHS2 2011/65/EU	Title: PLUG ASSEMBLY, HIGH FREQ END LAUNCH, SMA, .010 MIL PIN
	UNLESS OTHERWISE SPECIFIED UNITS: INCH .XX ±.02 .XXX ±.005 ANGLES ±2°	Model No. 142-0861-851
	Size B / DO NOT SCALE DRAWING / Date: 11/3/2014	Sheet 1 of 1

Please read our datasheet & drawing disclaimer here.

Downloaded from Arrow.com.