







PRODUCT NUMBER	SERIES NAME	PITCH
20020704-GXXXXXXLF	10-500	5.00 mm







POLE		2	3	4	5	6	7	8
Dim A		10.0[.394"]	15.0[.590"]	20.0[.787"]	25.0[.984"]	30.0[1.181"]	35.0[1.377"]	40.0[1.574"]
Dim B		5.0[.196"]	10.0[.394"]	15.0[.590"]	20.0[.787"]	25.0[.984"]	30.0[1.181"]	35.0[1.377"]
Tol.	±0.15[.006"]							±0.25[.010"]
POLE	9	10	11	12	13	14	15	16
Dim A	45.0[1.771"]	50.0[1.968"]	55.0[2.165"]	60.0[2.362"]	65.0[2.559"]	70.0[2.755"]	75.0[2.952"]	80.0[3.149"]
Dim B	40.0[1.574"]	45.0[1.771"]	50.0[1.968"]	55.0[2.165"]	60.0[2.362"]	65.0[2.559"]	70.0[2.755"]	75.0[2.952"]
Tol.	±0.25[.010"]				±0.30[.012"]			
POLE	17	18	19	20	21	22	23	24
Dim A	85.0[3.346"]	90.0[3.543"]	95.0[3.74"]	100.0[3.937"]	105.0[4.133"]	110.0[4.330"]	115.0[4.527"]	120.0[4.724"]
Dim B	80.0[3.149"]	85.0[3.346"]	90.0[3.543"]	95.0[3.74"]	100.0[3.937"]	105.0[4.133"]	110.0[4.330"]	115.0[4.527"]
Tol.	±0.30[.012"]		±0.40[.016"]					

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
litr	ecn	no	dr	date	tolerances unless otherwise specified		title
c					angles		TERMINAL BLOCK FIXED POWER PLUG, 45 DEGREE
					inches	scale	dwg no
					X±0.5		sheet 2 of 3
					X.X±0.3		size
					X±1"		20020704
					X.XX±0.1		A4
					dr WENDY CHEN 081610		type
					enr JASON HSU 081610		CUSTOMER Drawing
					chr GARY HSIEH 081610		
					appd JOSEPH HSIA 081610		
sheet index	revision	sheet					



PRODUCT NUMBER	SERIES NAME	PITCH
20020704-HXXXXXXLF	10-508	5.08 mm



POLE		2	3	4	5	6	7	8
Dim A		10.16[.400"]	15.24[.600"]	20.32[.800"]	25.4[1.000"]	30.48[1.200"]	35.56[1.400"]	40.64[1.600"]
Dim B		5.08[.200"]	10.16[.400"]	15.24[.600"]	20.32[.800"]	25.4[1.000"]	30.48[1.200"]	35.56[1.400"]
Tol.		±0.15[.006"]						±0.25[.010"]
POLE		9	10	11	12	13	14	15
Dim A		45.72[1.800"]	50.8[2.000"]	55.88[2.200"]	60.96[2.400"]	66.04[2.600"]	71.12[2.800"]	76.2[3.000"]
Dim B		40.64[1.600"]	45.72[1.800"]	50.8[2.000"]	55.88[2.200"]	60.96[2.400"]	66.04[2.600"]	71.12[2.800"]
Tol.		±0.25[.010"]				±0.30[.012"]		
POLE		17	18	19	20	21	22	23
Dim A		86.36[3.400"]	91.44[3.600"]	96.52[3.800"]	101.6[4.000"]	106.68[4.200"]	111.76[4.400"]	116.84[4.600"]
Dim B		81.28[3.200"]	86.36[3.400"]	91.44[3.600"]	96.52[3.800"]	101.6[4.000"]	106.68[4.200"]	111.76[4.400"]
Tol.		±0.30[.012"]			±0.40[.016"]			

mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK	
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title	
c					angles X±1°	X.XX±0.1	TERMINAL BLOCK FIXED POWER PLUG, 45 DEGREE	
					dr	WENDY CHEN 081610	dwg no	
					engr	JASON HSU 081610	sheet 3 of 3	
					chr	GARY HSIEH 081610	20020704	
					appd	JOSEPH HSIA 081610	A4	
sheet index	revision sheet						type CUSTOMER Drawing	