



Part Number : [1300270047](#)
Product Description : Micro-Change (M12) Single-Ended Cordset, 5 Poles, Female (Straight) to Pigtail, 22 AWG, DeviceNet Cable Plus Drain, 0.50m (1.64') Length
Series Number : 130027
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : DND20A-M005



Documents and Resources

Drawings
[1300270047_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130027
Description	Micro-Change (M12) Single-Ended Cordset, 5 Poles, Female (Straight) to Pigtail, 22 AWG, DeviceNet Cable Plus Drain, 0.50m (1.64') Length
IP Rating	IP67
Product Name	DeviceNet, Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	78678830005

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	7.24mm (.285")
Cable Length	0.50m (1.64')
Color - Cable Jacket	Gray
Connector End A	Micro-Change (M12)
Connector End B	Pigtail

Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	52.550/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Shielded-Twisted Pair
Wire Size (AWG)	22

This document was generated on May 26, 2026