


# Intel® Core™ Ultra Processors


# conga-TC700



## COM Express®


- Intel® performance hybrid architecture with up to 14 cores and 22 threads
- Integrated Intel® Arc™ Graphics - entry level discrete graphics performance up to 128EUs
- Intel® AI Boost – Integrated NPU accelerator
- Up to 96 GB RAM with in-band ECC
- PCI Express Gen 4 | USB 4


<b>Form factor</b>	COM Express® Compact   Type 6 connector pinout	
<b>CPUs</b>	Intel® Core™ Ultra Processors Meteor Lake-U/H (H-Series, U-Series)	
<b>DRAM</b>	2 SO-DIMM sockets for DDR5 memory modules up to 48 GB each (max. 96 GB RAM system capacity)   up to 5600 MT/s   in-band ECC	
<b>Mass Storage</b>	NVMe x4 SSD (optional) up to 1 TB capacity	
<b>Graphics</b>	Intel® Arc™ Graphics architecture   up to 8 X <sup>e</sup> Cores with 128 EUs	
<b>AI Acceleration</b>	Integrated NPU accelerator on all part numbers	
<b>Display</b>	Up to 3x DDI (2x shared with USB4)   LVDS or eDP   4x independent displays up to 8k	
<b>Ethernet</b>	2.5 GbE with TSN support via Intel® i226 Ethernet controller series	
<b>I/O Interfaces</b>	Up to 8 PCIe Gen5 PEG (H-Series) or up to 2x4 PCIe Gen4 PEG (U-Series)   up to 8 PCIe Gen4   up to 2x USB4   4x USB 3.2 Gen2 (incl. USB 2.0) + 8x USB 2.0   up to 2x SATA   2x UART   GPIOs   GP SPI   LPC   SM Bus   I2C	
<b>Audio</b>	HDA	
<b>congatec Board controller</b>	Next Gen 6 congatec Board Controller   Multi Stage Watchdog   non-volatile User Data Storage   Manufacturing and Board Information   Board Statistics I <sup>2</sup> C bus (fast mode, 400 kHz, multi-master)   Power Loss Control   Hardware Health Monitoring   POST Code Redirection	
<b>Embedded BIOS Feature</b>	AMI Aptio® UEFI firmware   64 Mbyte serial SPI with congatec Embedded BIOS feature   OEM Logo   OEM CMOS default settings   LCD Control   Display Auto Detection   Backlight Control   Flash Update	
<b>Security</b>	Trusted Platform Module (TPM 2.0)	
<b>Power Management</b>	ACPI 6.0 with battery support	
<b>Operating Systems</b>	Microsoft® Windows 11 IoT Enterprise   Microsoft® Windows 11   Microsoft® Windows 10 IoT Enterprise   Linux   Yocto	
<b>Hypervisor</b>	RTS Real-Time Hypervisor	
<b>Temperature</b>	Embedded Temp.: Operating 0°C to 60°C	Storage -20°C to 80°C
<b>Humidity</b>	Operating 10% to 90% r. H. non cond.	Storage 5% to 95% r. H. non cond.
<b>Size</b>	95 x 95 mm	



[www.congatec.com](http://www.congatec.com)

# conga-TC700 | Block Diagram



 Assembly option – only available on request

\*) U-Series: If assembly option for NVMe is used PEG port capability is 1x4 on PEG[0:3]

# conga-TC700 | Modules Order Information

Article	PN	Description
conga-TC700/ultra7-155H	045600	COM Express Type 6 Compact module based on Intel® Core™ Ultra 7 processor with 6 P-cores and 8 E-cores   P-cores 1.4Ghz up to 4.8GHz (turbo)   E-Cores 0.9GHz up to 3.8GHz (turbo)   Integrated NPU   24MB Intel® Smart Cache   Intel® Arc™ graphics with 8 X <sup>e</sup> Cores (128 EU)   Dual channel SODIMM DDR5 5600 MT/s memory interface   Intel® code name Meteor Lake-H
conga-TC700/ultra5-125H	045601	COM Express Type 6 Compact module based on Intel® Core™ Ultra 5 processor with 4 P-cores and 8 E-cores   P-cores 1.2GHz up to 4.5GHz (turbo)   E-cores 0.7GHz up to 3.6GHz (turbo)   Integrated NPU   18MB Intel® Smart Cache   Intel® Arc™ graphics with 7 X <sup>e</sup> Cores (112 EU)   Dual channel SODIMM DDR5 5600 MT/s memory interface   Intel® code name Meteor Lake-H
conga-TC700/ultra7-155U	045610	COM Express Type 6 Compact module based on Intel® Core™ Ultra 7 processor with 2 P-cores and 8 E-cores   P-cores 1.7Ghz up to 4.8GHz (turbo)   E-cores 1.2GHz up to 3.8GHz (turbo)   Integrated NPU   12MB Intel® Smart Cache   Intel® Graphics with 4 X <sup>e</sup> Cores (64 EU)   Dual channel SODIMM DDR5 5600 MT/s memory interface   Intel® code name Meteor Lake-U
conga-TC700/ultra5-125U	045611	COM Express Type 6 Compact module based on Intel® Core™ Ultra 5 processor with 2 P-cores and 8 E-cores   P-cores 1.3Ghz up to 4.3GHz (turbo)   E-cores 0.8GHz up to 3.6GHz (turbo)   Integrated NPU   12MB Intel® Smart Cache   Intel® Graphics with 4 X <sup>e</sup> Cores (64 EU)   Dual channel SODIMM DDR5 5600 MT/s memory interface   Intel® code name Meteor Lake-U

# conga-TC700 | Accessories Order Information

Article	PN	Description
conga-TC700/CSA-HP-B	045650	Standard active cooling solution for high performance COM Express module conga-TC700 with integrated heat pipes, 25.5mm height and integrated 12V fan. All standoffs are with 2.7mm bore hole.
conga-TC700/CSA-HP-T	045651	Standard active cooling solution for high performance COM Express module conga-TC700 with integrated heat pipes, 25.5mm height and integrated 12V fan. All standoffs are M2.5mm threaded.
conga-TC700/CSP-HP-B	045652	Standard passive cooling solution for high performance COM Express module conga-TC700 with integrated heat pipes, 24.7mm height. All standoffs are with 2.7mm bore hole.
conga-TC700/CSP-HP-T	045653	Standard passive cooling solution for high performance COM Express module conga-TC700 with integrated heat pipes, 24.7mm height. All standoffs are M2.5mm threaded.
conga-TC700/HSP-HP-B	045654	Standard heatspreader for high performance COM Express module conga-TC700 with integrated heat pipes, 11mm height. All standoffs are with 2.7mm bore hole.
conga-TC700/HSP-HP-T	045655	Standard heatspreader for high performance COM Express module conga-TC700 with integrated heat pipes, 11mm height. All standoffs are M2.5mm threaded.
conga-TEVAL/COMe 3.0	065810	Evaluation carrier board for COM Express Type 6 revision 3.0 modules.
conga-TEVAL/COMe 3.1	065820	Evaluation carrier board for COM Express Type 6 revision 3.1 modules.
DDR5-SODIMM-5600 (8GB)	068930	DDR5 SODIMM memory module with up to 5600 MT/s and 8GB RAM, commercial temp 0°C to +60°C
DDR5-SODIMM-5600 (16GB)	068931	DDR5 SODIMM memory module with up to 5600 MT/s and 16GB RAM, commercial temp 0°C to +60°C
DDR5-SODIMM-5600 (32GB)	068932	DDR5 SODIMM memory module with up to 5600 MT/s and 32GB RAM, commercial temp 0°C to +60°C
DDR5-SODIMM-5600 (48GB)	068933	DDR5 SODIMM memory module with up to 5600 MT/s and 48GB RAM, commercial temp 0°C to +60°C
DDR5-SODIMM-5600 (8GB) / i-temp	068934	DDR5 SODIMM memory module with up to 5600 MT/s and 8GB RAM, industrial temp -40°C to +85°C
DDR5-SODIMM-5600 (16GB) / i-temp	068935	DDR5 SODIMM memory module with up to 5600 MT/s and 16GB RAM, industrial temp -40°C to +85°C
DDR5-SODIMM-5600 (32GB) / i-temp	068936	DDR5 SODIMM memory module with up to 5600 MT/s and 32GB RAM, industrial temp -40°C to +85°C