

CATALOG LISTING
602HE126-6B
PAGE 1 OF 1
RELEASE NO. PR-23263
REPLACES

ISSUE
3




REVISIONS

DDM/CAD
DRAWN

JAK 4 MAR 98
CHECK

JJA 12 MAR 98
CHECK

JAK 4 MAR 98
CHECK



CIRCUIT DIAGRAM

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION	
CHARACTERISTICS		ELECTRICAL DATA	
OPERATING FORCE ——— 5-12 LB		CONTACT ARRANGEMENT	
FULL OVERTRAVEL FORCE --- 30 LB MAX		2X S P D T GOLD CONTACTS	
RELEASE FORCE ——— 3 LB MIN		LOAD	
PRETRAVEL ——— .040 MAX		28 VDC	
DIFFERENTIAL TRAVEL — .020 MAX		SEA LEVEL & 50,000 FT.	
OVERTRAVEL ——— .100 MIN		RES	
		1.0	
		IND	
		0.5	
		MOTOR	
		WEIGHT	

- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 5
 - 3 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 INCH OF PLUNGER TRAVEL
 - 4 - CIRCUIT DIAGRAM, AND CATALOG LISTING SHOWN ON NAMEPLATE
 - 5 - REPLACEMENT MOUNTING HARDWARE - PACKET 19PA9
 - 6 - FOR OPERATION IN TEMPERATURE OF MINUS 65°F TO PLUS 257°F
 - 7 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805
 - 8 - ENCLOSURE FINISHED WITH WHITE EPOXY BASED ENAMEL COLOR COLOR NO. 37875 PER FEDERAL STANDARD 595

ANSI Y14.5M-1982 APPLIES