

Part Number : 640050600
Product Description : Crimp Head for the AT-200 Pneumatic Hand Tool
Series Number : 207126
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools
Engineering Part Number : AT-7000

Documents and Resources

Tooling Specifications

ATS-640050600-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per ED/30/2017 (7 July 2017)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207126
Description	Crimp Head for the AT-200 Pneumatic Hand Tool
Comments	Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Air Tool
Tool Type	Pneumatic Hand Tool
UPC	756054560402
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
AT-200 Hand Held Pneumatic Tool, Without Crimp Dies	192790001

Applicable Parts

Description	Part Number
Closed-End Insulated Splice for 16-10 AWG Wire	191600002
Closed-End Insulated Splice for 22-14 AWG Wire, Clear	191600012

This document was generated on May 05, 2026

Downloaded from Arrow.com.