




PRODUCT NUMBER	PITCH
YExx21x000J0G	5.08mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item (a) Terminal housing: Thermoplastic (UL 94V-0)
- Item (b) Clamp: Brass, Ni plated
- Item (c) Solder pin: Brass, Tin plated
- Item (d) Terminal screw: Steel, Zinc plating"-slot type

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire (AWG): 12-24
- Stranded wire (AWG): 12-24
- Torque (Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C ± 5°C / 5 Sec
- Safety Approval: 

DIMENSION

Dim L	Nx5.08
Dim B	(N-1)x5.08

N=Number of poles

Poles	Tolerance
2p~6p	±0.15
7p~12p	±0.25
13p~18p	±0.35
19p~24p	±0.40

PART NO.: YE xx 2 1 x 0 00J0 G

End stackable	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
0	2	Black (RAL9005)	
02	2 poles	Red (RAL3001/D)	
03	3 poles	Orange (RAL2011/P)	
...	...	Yellow (RAL1018/A)	
...	...	Green (RAL6018/T)	
24	24 poles	Blue (RAL5015/A)	
		Grey (RAL7035/D)	
		White (RAL1102)	
		Green (RAL6018/U)	

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection		product family																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
										TERMINAL BLOCK																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
					angles	X.±0.5				TERMINAL BLOCK																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
					X.X±0.3					RISING CLAMP, 180D WIRE INLET,END STACKABLE																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
					X*±1*				scale																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																												
					dr	EVIN ZHONG	041014																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														</