
Part Number : 5041893270
Series Number : 504189
Status : Active - Proprietary
Product Category : PCB Headers and Receptacles



Symbol and Footprint (Multi-Format)

Specifications

AS-504186-001-001.pdf

AS-504186-002-001.pdf

SPK-504189-001-001.pdf

PS-504186-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active - Proprietary
Category	PCB Headers and Receptacles
Series	504189
Description	Micro-Lock 1.25mm Pitch Dual-Row Right-Angle Header, Beige, 32 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Micro-Lock
UPC	887191185392

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V

Physical

Breakaway	No
Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Beige
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Nickel

Downloaded from Arrow.com.

Net Weight	1513.193/mg
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.20mm, 1.60mm
PC Tail Length	3.00mm
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Temperature Range - Operating	-25° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.25mm Pitch Micro-Lock Dual Row Crimp Housings	504186

Downloaded from Arrow.com.