All orders placed will be shipped out as usual, delivery times are expected to be affected due to COVID-19.Thank you for your continued support. Read More

Register to Get $10 Shipping Coupon



FireBeetle Covers-24×8 LED Matrix (Blue)

SKU:DFR0485 Brand:DFRobot Reward Points: 150

Quantity Based

QTY	DISCOUNT
5-9	
10-49	
50+	

* Model: White Blue Green Yellow Red

Quantity: - +

ADD TO CART

Frequently Bought Together

FireBeetle Covers-24×8 LED Matrix (Blue) + FireBeetl... Bluetooth) + Fir... (Supports Wi-Fi) + Fi... 328P with BLE4.1 + Eval... - Bluetooth 5.0 =

You have choosen:0
Total amount:

BUY IT NOW

INTRODUCTION

DFRobot FireBeetle is a low-power consumption micro-controller intentionally designed for Internet of Things (IoT). This series micro-controllers aims at IoT node of low-power consumption, attending to build the IoT hardware platform quickly and conveniently. There are three types of FireBeetle, containing Boards (main control), Covers (expansion boards) and related Accessories.
This 24×8 LED Matrix display is special designed for FireBeetle series. It supports low-power consumption mode and scrolling display. With HT1632C high performance LED driver chip, every led has independent register, which makes it easy to drive separately. It integrates a 256KHz RC clock, only 5uA under low-power mode, support 16 scale PWM brightness adjustment. This product also works with the other Arduino micrcontroller like Arduino UNO.

Build a talking Alarm Clock synced to Google calendars



Hardware Components:

DFPlayer - A Mini MP3 Player For Arduino

Downloaded from Arrow.com.

FireBeetle Covers-24×8 LED Matrix (Blue)

FireBeetle ESP32 IOT Microcontroller

Обзор DFRobot FireBeetle Covers-24x8 LED Matrix



SPECIFICATION

- Operating Voltage: 3.3~5V
- LED Color: Blue
- Drive Chip: HT1632C
- Working Current: 6~100mA
- Low-power Consumption: 5uA
- RC clock: 256KHz
- Chip Select (CS): D2, D3, D4, D5 selectable
- Serial Data Communication
- Support Arduino Library
- Support Scrolling display
- Interface mode: FireBeetle Series Compatible
- Operating Temperature: -10℃~+85℃
- Dimension: 24 × 58(mm)/0.94 x 2.28(inches)
- Weight: 26g

DOCUMENTS

Product WIKI
More Documents

SHIPPING LIST

- FireBeetle Covers-24x8 LED Matrix (Blue) x1
- 18pin-2.54mm Pin Header x2
- 18pin-2.54mm Female Pin Header x2

REVIEW

FAQ

0 Comments DFRobot Disqus' Privacy Policy Login

Recommend 1 Tweet Share Sort by Best

ırt the discussion...

Be the first to comment.

Downloaded from Arrow.com.

Subscribe Add Disqus to your site Do Not Sell My Data DISQUS

Sign up for exclusive offers!

Your email address →

Like us on

DFROBOT® DRIVE THE FUTURE

INFORMATION

- About Us
- Warranty
- Privacy Policy
- Shipping
- Payment
- FAQ

CUSTOMER SERVICE

- DFRobot Distributors
- Contact us
- Site Map

MY ACCOUNT

- Affiliates
- Specials
- Coupon

Downloaded from Arrow.com.