



DA(UL) Series

UL Approved *, Normally Open, High Voltage Relays - 10kV



- **10kV Isolation**
- **Low Contact Resistance**
- **PCB or Panel Mount**
- **HV connections via Flying Leads, Solder Turret (wire wrap), or 1/4" Spade Terminals**
- **Excellent AC characteristics**



Recently approved by UL, very high isolation voltages (up to 10kV) are achieved through the use of high vacuum reed switches with either Rhodium or Tungsten contacts and make these relays suitable for high reliability applications, such as cardiac defibrillators, test equipment and high voltage power supplies.

The Rhodium contact relays have low contact resistance, while the Tungsten contact relays can switch higher voltages.


PCB or Panel Mount, via Nylon studs, versions are available.

Connection options, for the HV, include PCB, solder turret(wire wrap), flying lead and 0.25" spade terminals.

Contact Specification			Unit			Condition			10kV SPNO			10kV SPNC			
Contact Type									N/O (normally open)			N/O (normally open)			
Contact Material									Rhodium Tungsten			Rhodium Tungsten			
Isolation across contacts			kV	DC or AC peak					10 10			10 10			
Switching Power Max.			W						50 50			50 50			
Switching Voltage Max.			V	DC or AC peak					1000 7000			1000 7000			
Switching Current Max.			A	DC or AC peak					3 2 3			2			
Carry Current Max			A	DC or AC peak					4 3 4			3			
Capacitance across contacts			pF	coil to screen grounded					<0.2 <0.2			<0.2 <0.2			
Lifetime operations				dry switching					10 ⁹ 10 ⁹			10 ⁹ 10 ⁹			
				50W switching					10 ⁶ 10 ⁶			10 ⁶ 10 ⁶			
Contact Resistance			mΩ	max (typical)					50 (15) 250(100)			50 (15) 250(100)			
Insulation Resistance				Ωmin (typical)					10 ¹⁰ (10 ¹³)			10 ¹⁰ (10 ¹³)			
Coil Specification									5V	12V	24V	5V	12V	24V	
Must Operate Voltage			V	DC					3.7 9 20			3.7 9 20			
Must Release Voltage			V	DC					0.5 1.25 4			0.5 1.25 4			
Operate Time			ms	diode fitted					3.0 3.0 3.0			2.0 2.0 2.0			
Release Time			ms	diode fitted					2.0 2.0 2.0			3.0 3.0 3.0			
Resistance			Ω						28 150 780			38 240 925			
Relay Specification															
Isolation contact/coil			kV						17			17			
Insulation resistance contact to all terminals				Ωmin (typical)					10 ¹⁰ (10 ¹³)			10 ¹⁰ (10 ¹³)			
Environmental Operating Temp range			°C						-20 to +70			-20 to +70			

*Consult factory for UL ratings

Part Numbering System



Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Email:sales@cynergy3.com

ISO9001 CERTIFIED
DA(UL) 2016

www.cynergy3.com


© 2016 Cynergy3 Components, All Rights Reserved. Specifications are subject to change without prior notice. Cynergy3 Components and the Cynergy3 Components logo are trademarks of Cynergy3 Components Limited.




MECHANICAL

STANDARD

(e.g. DAT71210U)




CIRCUIT DIAGRAMS (ALL VARIANTS)



NOTE: COIL POLARITY IS NOT SIGNIFICANT


PANEL MOUNT

(e.g. DAT71210PU)



FLYING LEAD


(e.g. DAT71210FU)



NOTE: PINS WHICH ARE NOT NUMBERED HAVE NO ELECTRICAL CONNECTION.

TURRET (Wire Wrap)

(e.g. DAT71210TU)




NOTE: PINS WHICH ARE NOT NUMBERED HAVE NO ELECTRICAL CONNECTION.

SPADE TYPE

(e.g. DAT71210SU)

'S' Suffix denotes the 0.250" 'Push On' blade connectors, M4 fixing bolts and Epoxy potting.



Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Email: sales@cynergy3.com

ISO9001 CERTIFIED

www.cynergy3.com

© 2016 Cynergy3 Components, All Rights Reserved. Specifications are subject to change without prior notice. Cynergy3 Components and the Cynergy3 Components logo are trademarks of Cynergy3 Components Limited.