



HUS876 1,6/0,8

Article number: 301-60160



Images (1)



This product is not available anymore.
Please contact our sales team. >

Features

HUS876 tubing has UL-224 VW1 approval, ensuring a high level of flame retardancy. It is easy to apply because it has a high degree of flexibility and also has good mechanical and chemical properties.

It is also possible to print onto HUS876 tubing.

Certifications & Approvals



Application

HUS876 is used where high flame retardancy is required. It is very versatile because of its good mechanical and chemical properties, so it is used for insulation, mechanical protection, strain relief and marking.

Base Data

Colour	Black (BK)
GLOBAL PART DESCRIPTION	HUS876 1,6/0,8-PO-X-BK
Pack Cont.	300 m
Package Quantity per	metre
Shrink Ratio	2:1
Size	1/16 "
Variant	Thin-Wall
With inner glue (Yes/No)	No

Product Dimensions

Longitudinal Change After Shrinkage	+/-5 %
Recov. ∅ d max.	0.8 mm
Supplied ∅ D min.	1.6 mm
Wall (WT)	0.45 mm

Material and Specifications

Dielectric Strength	20 kV/mm according to IEC 243
---------------------	-------------------------------

ELV compliant (Article 4 - 2) YES

Flammability	UL 224 VW-1
Hazardous good	No
Insulation Class	B (VDE 0530)
Material	Polyolefin, cross-linked (PO-X)
Min. Shrink Temperature - °C	+110 °C
Operating Temperature - °C	-55 °C to +125 °C
Specifications	   
Specifications	CSA, MIL-DTL-23053/5C, SAE - AMS - DTL-23053/5C, UL 224 VW-1

Logistics and Packaging



More Information



ETIM 5.0	EC000217
ETIM 6.0	EC000217

Competences




Heat shrink tubing


You are looking for the heat shrink tubing meeting your application requirements best? The key factors to which we owe our success are the unique and quite specific properties of our heat shrink tubing.

[Heat Shrink Tubing >](#)

Calculators



Calculator tool for Heat Shrink Tubing



Wall thickness calculator

Stay in touch with us!



Global Company

[About us](#)
[Worldwide](#)
[Philosophy](#)
[Environment & Quality](#)
[Corporate Social Responsibility](#)
[Product Development](#)
[E-Business](#)
[ACADEMY](#)
[Careers](#)

Products

Product overview
Cable Ties and Fixings
Insulation
Cable Protection Systems
Electrical Installation
Identification Systems
Application Tooling
Connectivity

Competences

Cable Ties
Heat Shrink Tubing
Industrial Identification
and Self-Adhesive Labels
Cable Protection
Conduits
Electrical Installation
Electrical tape
Wire connectors
Cable rods
Downlight covers
Cable jointing
Gel-filled cable joints
Cable Tie Guns
Connectivity Products
RFID tracking
Cable tie mounts
Thermal Transfer Printer
P-Clamp
Wiring ducts
Cable management high
temperature
applications

Markets & Industries

Automotive Industry
Solar plants
Wind turbines
Shipbuilding
Panel building
Rail industry
Food Industry
Chemical Industry
Aerospace Industry

Media Centre

Videos
Product Catalogue
2018/2019
Automotive Catalogue
2016/2017
Connectivity Catalogues
2016/2017
Brochures
Software & Drivers
Helatag & Helafix
Templates
Manuals & Operating
Instructions

Events

Update: 03/06/2018

You can easily accept or reject the cookies on this site by choosing one of the following links:

[I accept cookies](#)

[I refuse cookies](#)

[Contact](#) [Terms of Service](#) [Imprint](#) [Privacy Policy](#)

[Privacy statement](#)