



Part Number : [2067640100](#)
Product Description : ISM 868/915MHz Dipole Flexible Antenna, 100.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Series Number : 206764
Status : Active
Product Category : Antennas



Documents & Resources

Drawings

[Drawing 2067640100_sd.pdf](#)
[Packaging Design Drawing 2067640100-PK.pdf](#)

3D Models and Design Files


[3D Model 2067640100_stp.zip](#)

Specifications

[Application Specification 2067640100-AS.pdf](#)
[Product Specification 2067640100-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Antennas
Series	206764
Description	ISM 868/915MHz Dipole Flexible Antenna, 100.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Family	Industrial, Scientific and Medical (ISM) Antennas
Product Name	ISM 868/915 MHz Stand Alone
Protocol	LoRa, Neul, SigFox, Z-Wave, Zigbee
Type	Internal, ISM Antenna, LPWAN
UPC	191128789165

Electrical

Band#1 F_End (MHz)	870
Band#1 F_Start (MHz)	863
Band#2 F_End (MHz)	928
Band#2 F_Start (MHz)	902
Electrical Connectivity	Cable
Peak Gain (dBi)	1.2 @ 868/915 MHz
Return Loss - S11 (dB)	< -9
Total Efficiency	>70% @ 868/915 MHz

Physical

Cable Length	100.00mm
Length	87.40mm

Mounting Style	Adhesive
Net Weight	0.872/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	12.40mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
50 Ohms, MCRF, PCB Vertical Jack Receptacle, SMT, 1.25mm Mounted Height	<u>734120110</u>

This document was generated on Mar 26, 2024