

Specifications



Photo is representative



Eaton EFPLA1GJ333C012LH

Eaton FILM CAP EFPLA, 1600VDC, 0.033uF, J, 2LEADS, Size=26mmx15.5mmx6mm

General specifications

PRODUCT NAME	Eaton EFPLA metallized polypropylene film pulse capacitors
CATALOG NUMBER	EFPLA1GJ333C012LH
UPC	197162036258
PRODUCT LENGTH/DEPTH	26 mm
PRODUCT HEIGHT	15.5 mm
PRODUCT WIDTH	6 mm
PRODUCT WEIGHT	3.73 g
COMPLIANCES	RoHS Compliant

Product specifications

VOLTAGE RATING	1600 Vdc
IRMS	4 A
PEAK CURRENT	99 A
EQUIVALENT SERIES RESISTANCE (ESR)	20 mΩ @ 10 kHz
EQUIVALENT SERIES INDUCTANCE (ESL)	15 nH
DV/DT	3000 V/μ s
TEMPERATURE RATING	-55 °C to +105 °C
SIZE	26 mm x 6.0 mm x 15.5 mm
CAPACITANCE	0.033 μ F
GRADE	Automotive THB Grade IIIB

Resources

APPLICATION NOTES

[Understanding Eaton's film capacitors \(Safety, DC-Link, Pulse and AC-filtering\)](#)

[Eaton's film capacitors provide reliable EMI filtering in onboard chargers for electric vehicles](#)

[Eaton's film capacitors provide reliable EMI filtering in fast-charging xEV stations](#)

BROCHURES

[Eaton capacitors provide reliable EMI filtering in distributed solar inverters](#)

[Eaton offers standard and automotive-grade film capacitors for electronic applications](#)

SPECIFICATIONS AND DATASHEETS

[EFPLA Pulse film capacitor data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

