

SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N : **CL32A106KOTLNNF**
- Description : **CAP, 10 μ F, 16V, \pm 10%, X5R, 1210**

A. Samsung Part Number

CL **32** **A** **106** **K** **O** **T** **L** **N** **N** **F**
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

| | | | | | | | | | | |
|-------------------------|---------------------------------------|----------------------|-----------------------------------|----|----|-----------|----|--|--|--|
| ① Series | Samsung Multi-layer Ceramic Capacitor | | | | | | | | | |
| ② Size | 1210 (inch code) | L: | 3.2 ± 0.3 | mm | W: | 2.5 ± 0.2 | mm | | | |
| ③ Dielectric | X5R | ⑧ Thickness division | Low profile | | | | | | | |
| ④ Capacitance | 10 μF | Inner electrode | Ni | | | | | | | |
| ⑤ Capacitance tolerance | ±10 % | Termination | Cu | | | | | | | |
| ⑥ Rated Voltage | 16 V | Plating | Sn 100% (Pb Free) | | | | | | | |
| ⑦ Thickness | 1.6 ± 0.1 mm | ⑨ Product | Normal | | | | | | | |
| | | ⑩ Special | Reserved for future use | | | | | | | |
| | | ⑪ Packaging | Embossed Type, 13" reel (8,000ea) | | | | | | | |

B. Samsung Reliability Test and Judgement condition

| | Performance | Test condition |
|---|--|--|
| Capacitance | Within specified tolerance | 1kHz \pm 10% 1.0 \pm 0.2 Vrms |
| Tan δ (DF) | 0.1 max. | |
| Insulation Resistance | More than 100Mohm $\cdot\mu$ F | Rated Voltage 60~120 sec. |
| Appearance | No abnormal exterior appearance | Visual inspection |
| Withstanding Voltage | No dielectric breakdown or mechanical breakdown | 250% of the rated voltage |
| Temperature Characteristics | X5R (From -55 $^{\circ}$ C to 85 $^{\circ}$ C, Capacitance change should be within \pm 15%) | |
| Adhesive Strength of Termination | No peeling shall be occur on the terminal electrode | 500g \cdot F, for 10 \pm 1 sec. |
| Bending Strength | Capacitance change : within \pm 12.5% | Bending to the limit (1mm) with 1.0mm/sec. |
| Solderability | More than 75% of terminal surface is to be soldered newly | SnAg3.0Cu0.5 solder 245 \pm 5 $^{\circ}$ C, 3 \pm 0.3sec. (preheating : 80~120 $^{\circ}$ C for 10~30sec.) |
| Resistance to Soldering heat | Capacitance change : within \pm 7.5% Tan δ , IR : initial spec. | Solder pot : 270 \pm 5 $^{\circ}$ C, 10 \pm 1sec. |

| | Performance | Test condition |
|------------------------------------|---|--|
| Vibration Test | Capacitance change : within $\pm 5\%$ Tan δ , IR : initial spec. | Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours \times 3 direction (x, y, z) |
| Moisture Resistance | Capacitance change : within $\pm 12.5\%$ Tan δ : 0.125 max IR : More than 12.5M $\Omega \cdot \mu F$ | With rated voltage 40 $\pm 2^\circ C$, 90~95%RH, 500+12/-0 hour |
| High Temperature Resistance | Capacitance change : within $\pm 12.5\%$ Tan δ : 0.125 max IR : More than 25M $\Omega \cdot \mu F$ | With 150% of the rated voltage Max. operating temperature 1000+48/-0 hour |
| Temperature Cycling | Capacitance change : within $\pm 7.5\%$ Tan δ , IR : initial spec. | 1 cycle condition Min. operating temperature $\rightarrow 25^\circ C$ \rightarrow Max. operating temperature $\rightarrow 25^\circ C$ 5 cycles test |

C. Recommended Soldering method :

Reflow (Reflow Peak Temperature : 260+0/-5 $^\circ C$, 10sec. Max)

* For the more detail Specification, Please refer to the Samsung MLCC catalogue.