

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/22/19	


APPROVED: _____


DATE: _____ TITLE: _____






RECOMMENDED PCB LAYOUT







SPECIFICATIONS:

Material:

Insulator: (PA9T) Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Red

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Current rating: 1 Amp

Contact resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Dielectric withstanding: 500 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant

RoHS COMPLIANT

Positions: 04 thru 26

A = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	HR	2/22/19
CHECKED	LW	2/22/19
APPROVED		

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: .100 [2.54] MIN FLEX CONNECTOR MALE, STRAIGHT, PCB TYPE, TIN PLATED

SIZE	PART NO.	REV.
X	MPH-A2-XX-V-T	-

REF: S00111C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.