

### KW Series Precision Interchangeable Thermistors




#### Description

Littelfuse precision interchangeable thermistors are low cost, highly accurate, stable devices designed specifically for temperature sensing and control applications. They are particularly suited for uses where their precision interchangeability eliminates the necessity for costly individual circuit calibration.

#### Options

- Non-standard resistance values and tolerances
- Special encapsulants or probe housings
- Special lead materials and lengths

#### Dimensions




Dimensions shown in inches.

A	B	C	D
0.250" Nom	30 AWG 0.010"	0.095" Max	1.5" ±0.250"

#### Features

- High accuracy
- Fast thermal response
- Low cost
- Small size
- Epoxy encapsulated
- High stability
- Long life
- R/T Curve-matched

#### Part Numbering System



**Note:** Not all combinations of Part Number codes are available. Contact Littelfuse for details.

## KW Series Precision Interchangeable Thermistors

### Specifications

Part Number	Resistance Ohms @ 25°C	Accuracy (±°C) 0-70°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Dissipation Constant, Nominal (mW/°C)	Thermal Time Constant, Max. - Still Air (seconds)	Thermal Time Constant, Max. - Well Stirred Oil (seconds)	Temperature Rating (°C)	Storage & Operation Temp for Best L/T Stability (°C)
KW102J2	1000	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW222J2	2252	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW302J2	3000	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW502J2	5000	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW602J2	6000	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW103G2	10000	±0.5°C	G	-4.04	3575	1	10	1	-80 to +135	-80 to +120
KW103J2	10000	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW203J2	20000	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW303J2	30000	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW503J2	50000	±0.5°C	J	-4.4	3892	1	10	1	-80 to +135	-80 to +120
KW503R2	50000	±0.5°C	R	-4.68	4140	1	10	1	-80 to +135	-80 to +120
KW104R2	100000	±0.5°C	R	-4.68	4140	1	10	1	-80 to +135	-80 to +120

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)