


MATERIAL NO.	ENGINEERING NO.	STUD SIZE	±.003/0.08 "S"
191930769	C-336-06R90	6	.146/3.71
191930752	C-336-08R90	8	.173/4.39
193230119	C6-336-M3R90	M3	.130/3.30







SALES DRAWING

NOTE(S):
Ⓑ 1. MATERIAL: C11000 COPPER
2. PLATING: ELECTROPLATE TIN
3. ALL DIMENSIONS IN INCHES/(MM).
4. WIRE SIZE: 12-10 AWG
2,5-6,0 MM^2
5. PARTS ARE ROHS COMPLIANT.

CONTROL STUD LOCATION
EC NO: IPG2017-1090 DRWN: GROJAS01 2017/06/06
CHKD: APPR: JMACNEIL 2017/07/17
DESCRIPTION
B
REV

QUALITY SYMBOLS
▼ - 0
Ⓒ - 0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .005
2 PLACES	± 0.13	± .01
1 PLACE	± 0.25	± ---
ANGULAR ±1/2°		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

SCALE 5:1 | DESIGN UNITS INCH | THIRD ANGLE PROJECTION | REVISE ON CAD ONLY
DIMENSION STYLE IN/MM
DRAWN BY DLM 03/09/10
CHECKED BY HEB 03/09/10
APPROVED BY RWD 03/09/10
TITLE: RING TONGUE TERMINAL VERSAKRIMP, RT ANGLE 12-10 AWG
MOLEX INCORPORATED
MATERIAL NO. (SEE CHART) | DOCUMENT NO. SD-19193-034 | SHEET NO. 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION B

tb_frame_B
rev. B1 2000/08/01

Downloaded from Arrow.com.