

MICROBEND MTR-7.5, SMA (male), SMPM-T (male), ruggedized, 50 Ohm, 26.5 GHz, 7.5 in, 190.5 mm

MICROBEND MTR-7.5

Properties

- Applicable up to 26.5 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 047 size Semi-Rigid cables
- Tightest bend radius in the MINIBEND family
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)



Product configuration

Type of cable	MICROBEND (32041E)
Type description connector A	29094CR-32-41
Series connector A	SMA, straight - plug
Type description connector B	29971TCR-32-41
Series connector B	SMPM-T, straight - plug
Length	190.5 mm
Length	7.5 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	26.5 GHz
VSWR max	1.5
Propagation velocity	70 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	19.08 dB	1.25	
2 GHz ... 18 GHz	14.72 dB	1.45	1.27 dB
18 GHz ... 26.5 GHz	13.98 dB	1.5	1.56 dB

MICROBEND MTR-7.5, SMA (male), SMPM-T (male), ruggedized, 50 Ohm, 26.5 GHz, 7.5 in, 190.5 mm

MICROBEND MTR-7.5

Mechanical data	
Cable diameter	1.91 mm
Static bending radius	1.52 mm
Dynamic bending radius	4.57 mm
Environmental data	
Operation temperature	-55 °C ... 125 °C
Ordering information	
Item number	Item description
80392249	MICROBEND MTR-7.5

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P46610 / Date of publication: 29.07.2026 / uncontrolled copy