

## LXY Series

- Adoption of innovative electrolyte and new technologies
- Endurance with ripple current : 2,000 to 8,000 hours at 105°C
- Solvent resistant type (see PRECAUTIONS AND GUIDELINES)
- RoHS2 Compliant
- AEC-Q200 compliant : Please contact Chemi-Con for more details, test data, information.




### SPECIFICATIONS


| Items                                                  | Characteristics                                                                                                                                                                                                                                                                       |                                                                                                      |      |      |      |      |      |  |  |  |
|--------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|------|------|------|------|------|--|--|--|
| Category                                               | -55 to +105℃                                                                                                                                                                                                                                                                          |                                                                                                      |      |      |      |      |      |  |  |  |
| Temperature Range                                      |                                                                                                                                                                                                                                                                                       |                                                                                                      |      |      |      |      |      |  |  |  |
| Rated Voltage Range                                    | 10 to 63V <sub>dc</sub>                                                                                                                                                                                                                                                               |                                                                                                      |      |      |      |      |      |  |  |  |
| Capacitance Tolerance                                  | ±20% (M) (at 20℃, 120Hz)                                                                                                                                                                                                                                                              |                                                                                                      |      |      |      |      |      |  |  |  |
| Leakage Current                                        | I=0.01CV or 3μA, whichever is greater.<br>Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20℃ after 2 minutes)                                                                                                                          |                                                                                                      |      |      |      |      |      |  |  |  |
| Dissipation Factor (tan δ)                             | Rated voltage (V <sub>dc</sub> )                                                                                                                                                                                                                                                      | 10V                                                                                                  | 16V  | 25V  | 35V  | 50V  | 63V  |  |  |  |
|                                                        | tan δ (Max.)                                                                                                                                                                                                                                                                          | 0.19                                                                                                 | 0.16 | 0.14 | 0.12 | 0.10 | 0.10 |  |  |  |
|                                                        | When nominal capacitance exceeds 1,000μF, add 0.02 to the value above for each 1,000μF increase. (at 20℃, 120Hz)                                                                                                                                                                      |                                                                                                      |      |      |      |      |      |  |  |  |
| Low Temperature Characteristics (Max. Impedance Ratio) | Z(-55℃)/Z(+20℃)                                                                                                                                                                                                                                                                       | 10 to 50V <sub>dc</sub> : 3max.                                                                      |      |      |      |      |      |  |  |  |
|                                                        |                                                                                                                                                                                                                                                                                       | 63V <sub>dc</sub> : 6max.                                                                            |      |      |      |      |      |  |  |  |
| (at 120Hz)                                             |                                                                                                                                                                                                                                                                                       |                                                                                                      |      |      |      |      |      |  |  |  |
| Endurance                                              | The following specifications shall be satisfied when the capacitors are restored to 20℃ after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage) for the specified period of time at 105℃.                        |                                                                                                      |      |      |      |      |      |  |  |  |
|                                                        | Time                                                                                                                                                                                                                                                                                  | ϕ 5 & 6.3 : 2,000hours ϕ 8 : 3,000hours ϕ 10 : 5,000hours ϕ 12.5 : 7,000hours ϕ 16 & 18 : 8,000hours |      |      |      |      |      |  |  |  |
|                                                        | Capacitance change                                                                                                                                                                                                                                                                    | ≤ ±20% of the initial value                                                                          |      |      |      |      |      |  |  |  |
|                                                        | D.F. (tan δ)                                                                                                                                                                                                                                                                          | ≤200% of the initial specified value                                                                 |      |      |      |      |      |  |  |  |
|                                                        | Leakage current                                                                                                                                                                                                                                                                       | ≤The initial specified value                                                                         |      |      |      |      |      |  |  |  |
| Shelf Life                                             | The following specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them for 1,000 hours at 105℃ without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4. |                                                                                                      |      |      |      |      |      |  |  |  |
|                                                        | Capacitance change                                                                                                                                                                                                                                                                    | ≤ ±20% of the initial value                                                                          |      |      |      |      |      |  |  |  |
|                                                        | D.F. (tan δ)                                                                                                                                                                                                                                                                          | ≤200% of the initial specified value                                                                 |      |      |      |      |      |  |  |  |
|                                                        | Leakage current                                                                                                                                                                                                                                                                       | ≤The initial specified value                                                                         |      |      |      |      |      |  |  |  |

### DIMENSIONS [mm]

#### Terminal Code : E



### PART NUMBERING SYSTEM



Please refer to "Product code guide (radial lead type)"

### RATED RIPPLE CURRENT MULTIPLIERS

#### Frequency Multipliers

| Capacitance(μF) | Frequency(Hz) | 120  | 1k   | 10k  | 100k |
|-----------------|---------------|------|------|------|------|
| 10 to 180       |               | 0.40 | 0.75 | 0.90 | 1.00 |
| 220 to 560      |               | 0.50 | 0.85 | 0.94 | 1.00 |
| 680 to 1,800    |               | 0.60 | 0.87 | 0.95 | 1.00 |
| 2,200 to 3,900  |               | 0.75 | 0.90 | 0.95 | 1.00 |
| 4,700 to 8,200  |               | 0.85 | 0.95 | 0.98 | 1.00 |

The endurance of capacitors is reduced with internal heating produced by ripple current at the rate of halving the lifetime with every 5°C rise.  
When long life performance is required in actual use, the rms ripple current has to be reduced.

### ◆STANDARD RATINGS

| WV<br>(V <sub>dc</sub> ) | Cap<br>(μF) | Case size<br>φD×L(mm) | Impedance<br>(Ω max./100kHz) |       | Rated<br>ripple<br>current<br>(mA <sub>rms</sub> /105°C,<br>100kHz) | Part No.           |
|--------------------------|-------------|-----------------------|------------------------------|-------|---------------------------------------------------------------------|--------------------|
|                          |             |                       | 20°C                         | -10°C |                                                                     |                    |
| 10                       | 82          | 5×11.5                | 0.75                         | 1.5   | 163                                                                 | ELXY100E□□820MEB5D |
|                          | 180         | 6.3×11.5              | 0.35                         | 0.70  | 273                                                                 | ELXY100E□□181MFB5D |
|                          | 220         | 6.3×15                | 0.25                         | 0.50  | 390                                                                 | ELXY100E□□221MF15D |
|                          | 330         | 8×12                  | 0.17                         | 0.34  | 445                                                                 | ELXY100E□□331MH12D |
|                          | 390         | 10×12.5               | 0.12                         | 0.24  | 625                                                                 | ELXY100E□□391MJC5S |
|                          | 470         | 8×15                  | 0.13                         | 0.26  | 555                                                                 | ELXY100E□□471MH15D |
|                          | 680         | 8×20                  | 0.095                        | 0.19  | 740                                                                 | ELXY100E□□681MH20D |
|                          | 680         | 10×16                 | 0.084                        | 0.17  | 825                                                                 | ELXY100E□□681MJ16S |
|                          | 1,000       | 10×20                 | 0.062                        | 0.13  | 1,040                                                               | ELXY100E□□102MJ20S |
|                          | 1,200       | 10×25                 | 0.052                        | 0.11  | 1,260                                                               | ELXY100E□□122MJ25S |
|                          | 1,500       | 10×30                 | 0.044                        | 0.088 | 1,440                                                               | ELXY100E□□152MJ30S |
|                          | 1,800       | 12.5×20               | 0.046                        | 0.092 | 1,340                                                               | ELXY100E□□182MK20S |
|                          | 2,200       | 12.5×25               | 0.034                        | 0.068 | 1,690                                                               | ELXY100E□□222MK25S |
|                          | 2,700       | 12.5×30               | 0.030                        | 0.060 | 1,950                                                               | ELXY100E□□272MK30S |
|                          | 3,300       | 12.5×35               | 0.024                        | 0.048 | 2,220                                                               | ELXY100E□□332MK35S |
|                          | 3,300       | 16×20                 | 0.038                        | 0.076 | 1,630                                                               | ELXY100E□□332ML20S |
|                          | 3,900       | 12.5×40               | 0.022                        | 0.044 | 2,390                                                               | ELXY100E□□392MK40S |
|                          | 3,900       | 16×25                 | 0.028                        | 0.056 | 2,070                                                               | ELXY100E□□392ML25S |
| 16                       | 56          | 5×11.5                | 0.75                         | 1.5   | 163                                                                 | ELXY160E□□560MEB5D |
|                          | 120         | 6.3×11.5              | 0.35                         | 0.70  | 273                                                                 | ELXY160E□□121MFB5D |
|                          | 180         | 6.3×15                | 0.25                         | 0.50  | 390                                                                 | ELXY160E□□181MF15D |
|                          | 270         | 8×12                  | 0.17                         | 0.34  | 445                                                                 | ELXY160E□□271MH12D |
|                          | 270         | 10×12.5               | 0.12                         | 0.24  | 625                                                                 | ELXY160E□□271MJC5S |
|                          | 330         | 8×15                  | 0.13                         | 0.26  | 555                                                                 | ELXY160E□□331MH15D |
|                          | 470         | 8×20                  | 0.095                        | 0.19  | 740                                                                 | ELXY160E□□471MH20D |
|                          | 470         | 10×16                 | 0.084                        | 0.17  | 825                                                                 | ELXY160E□□471MJ16S |
|                          | 680         | 10×20                 | 0.062                        | 0.13  | 1,040                                                               | ELXY160E□□681MJ20S |
|                          | 820         | 10×25                 | 0.052                        | 0.11  | 1,260                                                               | ELXY160E□□821MJ25S |
|                          | 1,200       | 10×30                 | 0.044                        | 0.088 | 1,440                                                               | ELXY160E□□122MJ30S |
|                          | 1,200       | 12.5×20               | 0.046                        | 0.092 | 1,340                                                               | ELXY160E□□122MK20S |
|                          | 1,500       | 12.5×25               | 0.034                        | 0.068 | 1,690                                                               | ELXY160E□□152MK25S |
|                          | 2,200       | 12.5×30               | 0.030                        | 0.060 | 1,950                                                               | ELXY160E□□222MK30S |
|                          | 2,200       | 16×20                 | 0.038                        | 0.076 | 1,630                                                               | ELXY160E□□222ML20S |
|                          | 2,700       | 12.5×35               | 0.024                        | 0.048 | 2,220                                                               | ELXY160E□□272MK35S |
|                          | 2,700       | 16×25                 | 0.028                        | 0.056 | 2,070                                                               | ELXY160E□□272ML25S |
|                          | 3,300       | 12.5×40               | 0.022                        | 0.044 | 2,390                                                               | ELXY160E□□332MK40S |
| 25                       | 39          | 5×11.5                | 0.75                         | 1.5   | 163                                                                 | ELXY250E□□390MEB5D |
|                          | 82          | 6.3×11.5              | 0.35                         | 0.70  | 273                                                                 | ELXY250E□□820MFB5D |
|                          | 120         | 6.3×15                | 0.25                         | 0.50  | 390                                                                 | ELXY250E□□121MF15D |
|                          | 150         | 8×12                  | 0.17                         | 0.34  | 445                                                                 | ELXY250E□□151MH12D |
|                          | 180         | 10×12.5               | 0.12                         | 0.24  | 625                                                                 | ELXY250E□□181MJC5S |
|                          | 220         | 8×15                  | 0.13                         | 0.26  | 555                                                                 | ELXY250E□□221MH15D |
|                          | 330         | 8×20                  | 0.095                        | 0.19  | 740                                                                 | ELXY250E□□331MH20D |
|                          | 330         | 10×16                 | 0.084                        | 0.17  | 825                                                                 | ELXY250E□□331MJ16S |
|                          | 470         | 10×20                 | 0.062                        | 0.13  | 1,040                                                               | ELXY250E□□471MJ20S |
|                          | 560         | 10×25                 | 0.052                        | 0.11  | 1,260                                                               | ELXY250E□□561MJ25S |
|                          | 820         | 10×30                 | 0.044                        | 0.088 | 1,440                                                               | ELXY250E□□821MJ30S |
|                          | 820         | 12.5×20               | 0.046                        | 0.092 | 1,340                                                               | ELXY250E□□821MK20S |
|                          | 1,000       | 12.5×25               | 0.034                        | 0.068 | 1,690                                                               | ELXY250E□□102MK25S |
|                          | 1,500       | 12.5×30               | 0.030                        | 0.060 | 1,950                                                               | ELXY250E□□152MK30S |
|                          | 1,500       | 16×20                 | 0.038                        | 0.076 | 1,630                                                               | ELXY250E□□152ML20S |
|                          | 1,800       | 12.5×35               | 0.024                        | 0.048 | 2,220                                                               | ELXY250E□□182MK35S |
|                          | 1,800       | 16×25                 | 0.028                        | 0.056 | 2,070                                                               | ELXY250E□□182ML25S |
|                          | 2,200       | 12.5×40               | 0.022                        | 0.044 | 2,390                                                               | ELXY250E□□222MK40S |
| 35                       | 27          | 5×11.5                | 0.75                         | 1.5   | 163                                                                 | ELXY350E□□270MEB5D |
|                          | 56          | 6.3×11.5              | 0.35                         | 0.70  | 273                                                                 | ELXY350E□□560MFB5D |
|                          | 82          | 6.3×15                | 0.25                         | 0.50  | 390                                                                 | ELXY350E□□820MF15D |
|                          | 120         | 8×12                  | 0.17                         | 0.34  | 445                                                                 | ELXY350E□□121MH12D |
|                          | 120         | 10×12.5               | 0.12                         | 0.24  | 625                                                                 | ELXY350E□□121MJC5S |
|                          | 180         | 8×15                  | 0.13                         | 0.26  | 555                                                                 | ELXY350E□□181MH15D |
|                          | 220         | 8×20                  | 0.095                        | 0.19  | 740                                                                 | ELXY350E□□221MH20D |
|                          | 220         | 10×16                 | 0.084                        | 0.17  | 825                                                                 | ELXY350E□□221MJ16S |
|                          | 330         | 10×20                 | 0.062                        | 0.13  | 1,040                                                               | ELXY350E□□331MJ20S |
|                          | 390         | 10×25                 | 0.052                        | 0.11  | 1,260                                                               | ELXY350E□□391MJ25S |
|                          | 560         | 10×30                 | 0.044                        | 0.088 | 1,440                                                               | ELXY350E□□561MJ30S |
|                          | 560         | 12.5×20               | 0.046                        | 0.092 | 1,340                                                               | ELXY350E□□561MK20S |
|                          | 680         | 12.5×25               | 0.034                        | 0.068 | 1,690                                                               | ELXY350E□□681MK25S |
|                          | 1,000       | 12.5×30               | 0.030                        | 0.060 | 1,950                                                               | ELXY350E□□102MK30S |
|                          | 1,000       | 16×20                 | 0.038                        | 0.076 | 1,630                                                               | ELXY350E□□102ML20S |
|                          | 1,200       | 12.5×35               | 0.024                        | 0.048 | 2,220                                                               | ELXY350E□□122MK35S |
|                          | 1,200       | 16×25                 | 0.028                        | 0.056 | 2,070                                                               | ELXY350E□□122ML25S |
|                          | 1,500       | 12.5×40               | 0.022                        | 0.044 | 2,390                                                               | ELXY350E□□152MK40S |
| 50                       | 18          | 5×11.5                | 1.2                          | 2.4   | 129                                                                 | ELXY500E□□180MEB5D |
|                          | 39          | 6.3×11.5              | 0.54                         | 1.1   | 219                                                                 | ELXY500E□□390MFB5D |
|                          | 56          | 6.3×15                | 0.34                         | 0.68  | 310                                                                 | ELXY500E□□560MF15D |
|                          | 68          | 8×12                  | 0.30                         | 0.60  | 340                                                                 | ELXY500E□□680MH12D |
|                          | 82          | 8×15                  | 0.20                         | 0.40  | 470                                                                 | ELXY500E□□820MH15D |
|                          | 82          | 10×12.5               | 0.20                         | 0.40  | 480                                                                 | ELXY500E□□820MJC5S |
|                          | 120         | 8×20                  | 0.14                         | 0.28  | 610                                                                 | ELXY500E□□121MH20D |
|                          | 120         | 10×16                 | 0.13                         | 0.26  | 755                                                                 | ELXY500E□□121MJ16S |
|                          | 180         | 10×20                 | 0.088                        | 0.18  | 945                                                                 | ELXY500E□□181MJ20S |
|                          | 220         | 10×25                 | 0.073                        | 0.15  | 1,150                                                               | ELXY500E□□221MJ25S |
|                          | 330         | 10×30                 | 0.054                        | 0.11  | 1,260                                                               | ELXY500E□□331MJ30S |
|                          | 330         | 12.5×20               | 0.059                        | 0.12  | 1,190                                                               | ELXY500E□□331MK20S |
|                          | 470         | 12.5×25               | 0.044                        | 0.088 | 1,490                                                               | ELXY500E□□471MK25S |
|                          | 560         | 12.5×30               | 0.039                        | 0.078 | 1,720                                                               | ELXY500E□□561MK30S |
|                          | 680         | 12.5×35               | 0.033                        | 0.066 | 1,890                                                               | ELXY500E□□681MK35S |
|                          | 680         | 16×20                 | 0.050                        | 0.10  | 1,420                                                               | ELXY500E□□681ML20S |
|                          | 820         | 12.5×40               | 0.029                        | 0.058 | 2,030                                                               | ELXY500E□□821MK40S |
|                          | 820         | 16×25                 | 0.034                        | 0.068 | 1,880                                                               | ELXY500E□□821ML25S |
| 63                       | 10          | 5×11.5                | 1.9                          | 4.8   | 103                                                                 | ELXY630E□□100MEB5D |
|                          | 18          | 6.3×11.5              | 1.0                          | 2.5   | 161                                                                 | ELXY630E□□180MFB5D |
|                          | 33          | 6.3×15                | 0.61                         | 1.6   | 233                                                                 | ELXY630E□□330MF15D |
|                          | 47          | 8×12                  | 0.47                         | 1.2   | 274                                                                 | ELXY630E□□470MH12D |
|                          | 56          | 10×12.5               | 0.27                         | 0.68  | 418                                                                 | ELXY630E□□560MJC5S |
|                          | 68          | 8×15                  | 0.34                         | 0.85  | 360                                                                 | ELXY630E□□680MH15D |
|                          | 68          | 10×16                 | 0.21                         | 0.53  | 525                                                                 | ELXY630E□□680MJ16S |
|                          | 82          | 8×20                  | 0.21                         | 0.53  | 500                                                                 | ELXY630E□□820MH20D |
|                          | 120         | 10×20                 | 0.16                         | 0.40  | 650                                                                 | ELXY630E□□121MJ20S |
|                          | 150         | 10×25                 | 0.13                         | 0.33  | 783                                                                 | ELXY630E□□151MJ25S |
|                          | 180         | 10×30                 | 0.10                         | 0.25  | 960                                                                 | ELXY630E□□181MJ30S |
|                          | 220         | 12.5×20               | 0.11                         | 0.28  | 870                                                                 | ELXY630E□□221MK20S |
|                          | 270         | 12.5×25               | 0.074                        | 0.19  | 1,150                                                               | ELXY630E□□271MK25S |
|                          | 330         | 16×20                 | 0.085                        | 0.22  | 1,100                                                               | ELXY630E□□331ML20S |
|                          | 390         | 12.5×30               | 0.068                        | 0.17  | 1,280                                                               | ELXY630E□□391MK30S |
|                          | 470         | 12.5×35               | 0.063                        | 0.16  | 1,390                                                               | ELXY630E□□471MK35S |
|                          | 470         | 16×25                 | 0.055                        | 0.14  | 1,480                                                               | ELXY630E□□471ML25S |
|                          | 560         | 12.5×40               | 0.051                        | 0.13  | 1,530                                                               | ELXY630E□□561MK40S |

□□ : Enter the appropriate lead forming or taping code.