



Part Number : [5030913620](#)
Product Description : 2.00mm Pitch, iGrid PCB Header, Dual Row, Vertical, Through Hole, Gold (Au) Plating, Positive Lock, 36 Circuits, Tray, 3.20mm PC Tail Length, Natural, with PCB Locator
Series Number : 503091
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[5030913620 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[5030913620.dxf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	503091
Description	2.00mm Pitch, iGrid PCB Header, Dual Row, Vertical, Through Hole, Gold (Au) Plating, Positive Lock, 36 Circuits, Tray, 3.20mm PC Tail Length, Natural, with PCB Locator
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	iGrid
UPC	195842372917

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	36

Circuits (maximum)	36
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	2173.200/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.20mm, 1.60mm
PC Tail Length	3.20mm
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole
Unmated Height	12.00mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
iGrid Dual Row Receptacle	<u>501646</u>

Housings	
----------	--

This document was generated on Dec 29, 2025