


GL3ED8

ø3mm(T-1), Cylinder Type, Milky Diffusion, Dichromatic LED Lamp for Backlight/Indicator


Outline Dimensions

(Unit : mm)



Directive Characteristics

(Ta=25°C)



Absolute Maximum Ratings

(Ta=25°C)

Model No.	Emitting color	Material	Power dissipation P*1 (mW)	Forward current IF (mA)	Peak forward current IFM*2 (mA)	Derating factor (mA/°C)		Reverse voltage VR (V)	Operating temperature Topr (°C)	Storage temperature Tstg (°C)	Soldering temperature Tsol*3 (°C)
						DC	Pulse				
GL3ED8	Yellow-green	GaP	84	30	50	0.40	0.67	5	-25 to +85	-25 to +100	260
	Red	GaAsP on GaP	84	30	50	0.40	0.67	5			

*1 The value is specified under the condition that either color is lightened separately. When the both diodes are lightened simultaneously, the power dissipation of each diode should be less than the half of the value specified in this table.

*2 Duty ratio=1/10, Pulse width=0.1ms

*3 5s or less(At the position of 1.6mm or more from the bottom face of resin package)

Electro-optical Characteristics


(Ta=25°C)

Lens type	Model No.	Radiation color	Forward voltage V _F (V)		Peak emission wavelength		Luminous intensity		Spectrum radiation bandwidth		Reverse current		Terminal capacitance		Page for characteristics diagrams
			TYP	MAX	λ _p (nm) TYP	I _F (mA)	I _v (mcd) TYP	I _F (mA)	Δλ(nm) TYP	I _F (mA)	I _R (μA) MAX	V _R (V)	C _t (pF) TYP	(MHz)	
Milky diffusion	GL3ED8	Yellow-green	2.1	2.8	565	20	20	20	30	20	10	4	35	1	102
		Red	2.0	2.8	635	20	15	20	35	20	10	4	20	1	100


Characteristics Diagrams

PR,P series


Forward Current Derating Curve




Forward Current vs. Forward Voltage(Note)




Luminous Intensity vs. Ambient Temperature(Note)




Peak Forward Current Derating Curve



Luminous Intensity vs. Forward Current(Note)




Duty Ratio vs. Peak Forward Current




HD,D series


Forward Current Derating Curve




Forward Current vs. Forward Voltage(Note)




Luminous Intensity vs. Ambient Temperature(Note)




Peak Forward Current Derating Curve



Luminous Intensity vs. Forward Current(Note)









Duty Ratio vs. Peak Forward Current









Note) Characteristics shown in diagrams are typical values. (not assurance value)

Characteristics Diagrams

EG,E,F,C series



KG,K series



Note) Characteristics shown in diagrams are typical values. (not assurance value)


Taping Specifications

■ General Description

Sharp can supply tape-packaged LED lamps for automatic mounting. They will contribute to the high-efficiency mounting, high-precision, power saving. Please confirm before use because some products are not available in taping package.


■ Taping specification(Unit : mm, TYP. value)

Forming type




Parameter	Symbol	A	B	D
Case end height	H	23.35	19.5	21.5
Lead clinch height	H _O	16.0		
Tape width	W	18.0		
Adhesive tape width	W _O	13.0		
Product pitch	P	12.7		
Sprocket hole pitch	P _O	12.7		
Lead pitch	F	5.0		
Sprocket hole diameter	D _O	ø4.0		

Straight type



Parameter	Symbol	p	W
Case end height	H	18.0	23.35
Lead clinch height	H _O	—	
Tape width	W	18.0	
Adhesive tape width	W _O	13.0	
Product pitch	P	12.7	
Sprocket hole pitch	P _O	12.7	
Lead pitch	F	2.54	
Sprocket hole diameter	D _O	ø4.0	

Dichromatic emission type



Parameter	Symbol	Size (mm)
Case end height	H	19.5
Lead clinch height	H _O	—
Tape width	W	18.0
Adhesive tape width	W _O	13.0
Product pitch	P	12.7
Sprocket hole pitch	P _O	12.7
Lead pitch	F1, F2	2.54
Sprocket hole diameter	D _O	ø4.0

NOTICE

- The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
 - (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - Personal computers
 - Office automation equipment
 - Telecommunication equipment [terminal]
 - Test and measurement equipment
 - Industrial control
 - Audio visual equipment
 - Consumer electronics
 - (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:
 - Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
 - Traffic signals
 - Gas leakage sensor breakers
 - Alarm equipment
 - Various safety devices, etc.
 - (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - Space applications
 - Telecommunication equipment [trunk lines]
 - Nuclear power control equipment
 - Medical and other life support equipment (e.g., scuba).
- If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this publication.