

MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

SWITCH - BASIC

X113024-YA

REPLACES

0838

RELEASE NO

CHECK

CHECK

18 JUL 00


SAV

CHECK

00 JUN 68

RASTER

BROWN



2X 6-32 UNC X (.219) BINDING
HEAD TERMINAL SCREW AND
INTERNAL TOOTH LOCKWASHERS

NOTE

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF Ø.139 MAX ON 1.000±.002 CENTERS
② COVER BONDED TO SWITCH CASE

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE----- 14-22 OZ	CONTACT ARRANGEMENT	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE ----- 10 OZ MIN	SPNO	ONE PLACE	(.0)	±.030
DIFFERENTIAL TRAVEL----- .002-.0075	L23 20A 125, <u>250</u> OR 480 VAC	TWO PLACE	(.00)	±.015
OVERTRAVEL ----- .094 MIN	10A 125 VAC "L"	THREE PLACE	(.000)	±.005
	1HP 125 VAC, 2HP <u>250</u> VAC	ANGLES		±
	1/2A 125 VDC, 1/4A 250 VDC	WEIGHT	.064 LB	
	L288			
	L308			
	L315			
	20(3)A 250V ~ T85 5E4			