


## SKINTOP® MS

SKINTOP® MS, brass cable gland with maximum reliability, in areas where mechanical and chemical stability are critical



Good chemical resistance



Corrosion-resistant



Optimum strain relief



Robust



Temperature-resistant



Variety of approval certifications

### Benefits

Maximum reliability

Optimum strain relief

Wide, variable clamping ranges

### Application range

In areas where mechanical and chemical stability are critical

Chemical industry

Measurement and control technology

Machine and equipment manufacturing

Plant engineering

### Product Make-up

PG connection thread acc. to DIN 40430

Last Update (27.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SKINTOP® MS****Technical Data**

|                        |  |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000441<br>ETIM 5.0 Class-Description: Cable screw gland |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000441<br>ETIM 6.0 Class-Description: Cable screw gland |
| Caution:               | Refer to Appendix T21 for the installation dimensions and torques            |
| Material:              | Body: nickel-plated brass<br>Insert: polyamide<br>Sealing: CR<br>O-ring: NBR |
| Protection rating:     | IP 68 - 5 bar  |
| Temperature range:     | Dynamic: -25°C up to +100°C<br>Fixed: -40°C up to +100°C                     |

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



**SKINTOP® MS**

| Article number | Article designation / size | Ø F mm      | SW wrench size mm | Overall length C mm | Thread length D mm | Pieces / PU |
|----------------|----------------------------|-------------|-------------------|---------------------|--------------------|-------------|
| SKINTOP® MS    |                            |             |                   |                     |                    |             |
| 52015700       | PG 7                       | 2.0 - 6.5   | 14                | 25.0                | 5                  | 100         |
| 52015710       | PG 9                       | 4.0 - 8.0   | 17                | 29.0                | 6                  | 100         |
| 52015720       | PG 11                      | 4.0 - 10.0  | 20                | 32.0                | 6                  | 50          |
| 52015730       | PG 13,5                    | 5.0 - 12.0  | 22                | 34.0                | 6.5                | 50          |
| 52015740       | PG 16                      | 8.0 - 14.0  | 24                | 35.0                | 6.5                | 50          |
| 52015750       | PG 21                      | 11.0 - 18.0 | 30                | 40.0                | 7                  | 25          |
| 52015760       | PG 29                      | 16.0 - 25.0 | 40                | 48.0                | 8                  | 25          |
| 52015765       | PG 36                      | 19.0 - 32.0 | 50                | 62.0                | 15                 | 10          |
| 52015766       | PG 42                      | 28.0 - 38.0 | 57                | 62.0                | 15                 | 5           |
| 52015767       | PG 48                      | 34.0 - 44.0 | 64                | 62.0                | 15                 | 5           |

Last Update (27.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16