Welcome to TE.com, you are viewing information for visitors in United States CHOOSE ANOTHER SITE STAY ON THIS SITE

CV7370-000

222K163-25L-0



Raychem

TE Internal #: **CV7370-000**
TE Internal Description: **222K163-25L-0**

Molded Part Shape : **90°**
Molded Part Shape Code : **222**
Lipped : **Yes**
Material Code : **25**
Material Systems Code : **25**

Similar Products

ORDER SAMPLES

Compatible Parts & Tooling

We are here to help!
Get in touch with our product experts.

CHAT WITH US
EMAIL US
CALL US

Feedback

Documents | Features | Product Compliance

Product Drawings	222K163-25L-0 222K163-25L-0 English
Datasheets & Catalog Pages	1654025_Sec4_-25 ENG_CS_1654025_Sec4_-25_0313.pdf English
Product Specifications	RAYCHEM BRAND MOULDED COMPONENTS, LIGHT WEIGHT, FLAME RETARDED, SEMI-RIGID, HEAT SHRINKABLE, ELASTOMER (-25L) ENG_SS_RW-3040_2.pdf English
Product Environmental Compliance	Safety Datasheet ENG_MSDS_SDS0190-EC-ENG_2014-04-10.pdf English FRE_MSDS_SDS0190-EC-FRE_2014-04-10.pdf French Safety Datasheet GER_MSDS_SDS0190-EC-GER_2014-04-10.pdf German Safety Datasheet ITA_MSDS_SDS0190-EC-ITA_2014-04-10.pdf Italian Safety Datasheet NOR_MSDS_SDS0190-EC-NOR_2014-04-10.pdf Norwegian Safety Datasheet SPA_MSDS_SDS0190-EC-SPA_2014-04-10.pdf

Downloaded from Arrow.com.

Spanish

Safety Datasheet

SWE_MSDS_SDS0190-EC-SWE_2014-02-21_SDS190ECW.pdf Swedish

Safety Datasheet

DUT_MSDS_SDS0190-EC-DUT_2014-04-10.pdf Dutch

Safety Datasheet

DAN_MSDS_SDS0190-EC-DAN_2014-04-10.pdf Danish

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Shape : **90°**

Configuration Features

Lipped : **Yes**

Body Features

Material Code : **25**
Material Systems Code : **25**
Adhesive Pre-Coat : **No**
Material : **Fluid Resistant Modified Elastomer**

Dimensions

Cable Diameter Range : **9.9 – 22 mm [9.9 – 23 in]**
Connector or Backshell Outside Diameter :
1.26 in, 1.34 in, 1.42 in, 1.5 in, 1.57 in, 32 mm, 34 mm, 36 mm, 38 mm, 40 mm
Wire/Cable Outside Diameter :
.43 in, .47 in, .55 in, .63 in, .7 in, .787 in, 11 mm, 12 mm, 14 mm, 16 mm, 18 mm, 20 mm

Usage Conditions

Operating Temperature Range : **-75 – 150 °C [-103 – 302 °F]**

Operation/Application

Power Cable Accessory : **No**

Other

Molded Part Shape Code : **222**
Fluid/Chemical Resistance :
Long-Term Exposure at High Temperature
Adhesive Options : **/225 Precoat**
Adhesive Type : **Adhesive Purchased Separately**

EU RoHS Directive 2011/65/EU

This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).

Downloaded from Arrow.com.

2000/53/EC	
China RoHS 2 Directive MIIT Order No 32, 2016	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: **JAN 2019 (197)** Candidate List Declared Against: **JAN 2019 (197)**
Halogen Content	
Solder Process Capability	Not applicable for solder process capability
Statement of Compliance	Statement of Compliance pdf
Compliance Documents	There may be Environmental Compliance related documents on the DOCUMENTATION Tab
Disclaimer	This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Products with Similar Specs

View All Similar Products

Downloaded from Arrow.com.

THIS PRODUCT TOP RESULTS

THIS PRODUCT TOP RESULTS

HEAT SHRINK BOOTS
CV7370-000
222K163-25L-0



From **In-Stock**

Molded Part Shape : **90°**
Molded Part Shape Code : **222**
Lipped : **Yes**
Material Code : **25**
Material Systems Code : **25**

HEAT SHRINK BOOTS
202K163-25L-0
202K163-25L-0



From **In-Stock**

Molded Part Shape : **Straight**
Molded Part Shape Code : **202**
Lipped : **Yes**
Material Code : **25**
Material Systems Code : **25**


HEAT SHRINK BOOTS
202K174-25L-0
202K174-25L-0



From **In-Stock**

Molded Part Shape : **Straight**
Molded Part Shape Code : **202**
Lipped : **Yes**
Material Code : **25**
Material Systems Code : **25**

HEAT SHRINK BOOTS
202K163-25-0
202K163-25-0



From **In-Stock**

Molded Part Shape : **Straight**
Molded Part Shape Code : **202**
Lipped : **Yes**
Material Code : **25**
Material Systems Code : **25**

Downloaded from Arrow.com.