






This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

Customer Drawing



RECOMMENDED P.C.B. LAYOUT
TOLERANCE:±0.05MM



Dimensions

Positions	A	B	D	E
9	30.81	24.99	16.33	11.08
15	39.20	33.30	24.70	19.39
25	53.05	47.04	38.40	33.24
37	69.40	63.50	54.80	49.86



REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	08/28/18	IP
2	HK--	Added section A-A	08/30/18	IP

D-SUB TECHNICAL DATA

SHELL : Steel, 100u" min tin plated over 50u" min nickel over 50u" min Copper
BODY : PBT UL 94V-0 Color: Black
CONTACTS : Phosphor Bronze
30u" gold plated over 50u" min nickel on mating area.
100u" min tin over 50u" min nickel on termination area.
REAR NUT: Brass, Nickel plated.
ELECTRICAL : Voltage rating 250 V Rms
Current rating 3A.
Withstanding Voltage >1000 V Rms
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms max.
MARKING : Amphenol...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

RoHS Compliant	L	17TF	XX	0	2	1	0	0	Flange mounting option: 0= 3.05mm clear hole
Number of contact: 09-15-25-37									Board mounting option: 0= Without boardlock
Contact type: 0= Socket									Front screw plating: 1= Tin over nickel
Contact plating: 2= 30u" gold									

UNLESS OTHERWISE SPECIFIED TOLERANCES

	U.S.	METRIC
.X +/-		0.50
.XX +/-		0.30
.XXX +/-		0.20
FRACTIONS +/-		5°
ANGLES +/-		

FOR MATERIALS AND FINISHES
SEE NOTES

REMOVE SHARP EDGES


DIMENSIONS

U.S.	INCHES
METRIC	MM

APPROVAL	DATE
DRAWN Simon Chen	08/30/18
CHECKED Tony Tang	08/30/18
CHECKED	

DRAWING FILE :

ANGLE OF PROJECTION



Amphenol

TITLE

D-SUB connector, Press fit Series

SIZE DRAWING NO.

A4 L17TFXX02100

REV.

2

SCALE NONE

SHEET 1 OF 1