



Data Sheet | Item Number: 857-810

Temperature signal conditioner for thermocouples; Current and voltage output signal; Configuration via DIP switch; Supply voltage: 24 VDC; 6 mm module width; light gray

<https://www.wago.com/857-810>



Color: light gray




857-810
DIP Switch Adjustability

DIP Switch S1

Cold Junction Compensation	Sensor type	Output signal	Measurement Range Underflow	Measurement Range Overflow	Wire Break
on	J	0...20 mA	Lower limit of output range - 5%	Upper limit of output range + 2.5%	Upper limit of output range + 5%
off	K	4...20 mA	Lower limit of output range	Upper limit of output range + 2.5%	Upper limit of output range + 5%
		0...10 V	Lower limit of output range	Upper limit of output range	Upper limit of output range + 5%
		2...10 V	Lower limit of output range	Upper limit of output range	Upper limit of output range + 5%
		0...5 V	Lower limit of output range	Upper limit of output range	Lower limit of output range
		1...5 V			

DIP 9 and 10 n.c.
DIP Switch S2

Start Temperature										End Temperature									
1	2	3	4	5	6	7	8	9	10	1	2	3	4	5	6	7	8	9	10
0	50	100	150	200	250	300	350	400	450	500	550	600	650	700	750	800	850	900	950
...	...	...	...	...	...	...	...	...	...	...	...	...	...	...	...	...	...	...	...



Short description:

WAGO's temperature signal conditioner records signals from thermocouples (type J, K) and converts the temperature signal into a standard analog signal at the output.

Features:

- For type J and K thermocouples
- Cold junction compensation (On/Off)
- Calibrated measurement range switching
- Detects a sensor wire break
- Detects measurement range underflow/overflow
- Clipping capability for analog signal limitation to output end values
- 3-way electrical isolation with 2.5 kV test voltage

Technical data	
Configuration	Input
Configuration options	DIP switch
	Input signal type
	TC sensors



Input (TC sensors)	
Sensor types (TC)	Type J Type K
Temperature measurement range (TC)	-200 ... 1200 °C (Type J) -200 ... 1350 °C (Type K)
Measurement span (TC) min.	100 K
Cold junction compensation	ON/OFF (default: ON)
Cold junction error	3 K (typ. 2 K)

Output (analog)	
Output signal type	Current Voltage
Output signal (voltage)	0 ... 5 V 1 ... 5 V 0 ... 10 V 2 ... 10 V
Output signal (current)	0 ... 10 mA 2 ... 10 mA 0 ... 20 mA 4 ... 20 mA
Load impedance (voltage output)	≥ 2 kΩ
Load impedance (current output)	≤ 600 Ω

Signal processing	
Step response (typ.)	60 ms (cold junction compensation Off) 120 ms (cold junction compensation On)

Measurement error	
Transmission error (typ.)	≤ 0.1% at max. measurement span (type J, K)
Transmission error for the set measurement range	≤ (150 K/set measurement range [K]) %
Temperature coefficient	≤ 0.04 %/K

Power supply	
Power supply type	24 VDC
Nominal supply voltage U _s	24 VDC
Supply voltage range	±30 %
Current consumption at nominal supply voltage	≤ 40 mA

Safety and protection	
Protection type	IP20
Test voltage	
Test voltage (input/output/supply)	2.5 kVAC; 50 Hz; 1 min

Connection data	
Connection technology	Push-in CAGE CLAMP®
Solid conductor	0.08 ... 2.5 mm² / 28 ... 14 AWG
Fine-stranded conductor	0.34 ... 2.5 mm² / 22 ... 14 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches

Physical data	
Width	6 mm / 0.236 inches
Height	94 mm / 3.701 inches
Depth from upper-edge of DIN-rail	97.8 mm / 3.85 inches



Mechanical data		
Mounting type	DIN-35 rail	
Material data		
Color	light gray	
Insulation material (main housing)	Polyamide (PA66)	
Flammability class per UL94	V0	
Fire load	0.365 MJ	
Weight	35.5 g	
Environmental requirements		
Ambient temperature (operation)	-25 ... +70 °C	
Ambient temperature (storage)	-40 ... +85 °C	
Relative humidity	5 ... 95 % (no condensation permissible)	
Operating altitude (max.)	2000 m	
Standards and specifications		
Conformity marking	CE	
EMC immunity to interference	EN 61000-6-2	
EMC emission of interference	EN 61000-6-4	
Standards/specifications	DNV	
Commercial data		
Product Group	6 (INTERFACE ELECTRONIC)	
PU (SPU)	1 pcs	
Packaging type	Bag	
Country of origin	DE	
GTIN	4045454470135	
Customs tariff number	85437090300	
Product classification		
UNSPSC	41111970	
eCl@ss 10.0	27-21-01-29	
eCl@ss 9.0	27-20-02-06	
ETIM 9.0	EC002919	
ETIM 8.0	EC002919	
ECCN	NO US CLASSIFICATION	
Environmental Product Compliance		
CAS-No.	1303-86-2 1317-36-8 7439-92-1 75980-60-8 79-94-7	
REACH Candidate List Substance	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol Diboron trioxide Lead Lead monoxide Phosphine oxide, diphenyl(2,4,6-trimethylbenzoyl)-	
RoHS Compliance Status	Compliant,With Exemption	
RoHS Exemption	6(c) 7(a) 7(c)-I 7(c)-II	
SCIP notification number (Austria)	694a8dfe-c43e-47d6-ad52-996c633f9655	



Environmental Product Compliance	
SCIP notification number (Belgium)	296545de-031d-4d5e-a5a5-dfddc192cdf7
SCIP notification number (Bulgaria)	c1b7b523-92f8-47da-850c-8c4c882c490d
SCIP notification number (Czech Republic)	e269576b-40b6-4b8e-a730-b20f6c4642ba
SCIP notification number (Denmark)	adf6ed2d-abff-4125-bf6c-c121e8fca395
SCIP notification number (Finland)	5021c540-639b-4fdb-88aa-4c5ba154c53e
SCIP notification number (France)	ca2c2545-875b-4634-b7a2-589c69c41520
SCIP notification number (Germany)	ba87344e-9f0c-4f92-8d9b-a3c90deeb4cc
SCIP notification number (Hungary)	62c2d5b3-a430-476c-810d-c2bfb1e4d555
SCIP notification number (Italy)	7dccf9c7-af48-427e-8cf4-62ec1cfc9737
SCIP notification number (Netherlands)	9d300dab-2d6b-4501-8a24-bc26ad68f589
SCIP notification number (Poland)	Odd42d60-44a1-435a-b52e-47b29f5d6be4
SCIP notification number (Romania)	64b5849a-efc7-4fa8-9d9c-d6e400e9cc32
SCIP notification number (Sweden)	be28f513-6c89-4361-b6f3-1dba6122eca2

Approvals / Certificates

General approvals		Declarations of conformity and manufacturer's declarations
		
Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 508	E175199 Sec.4

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-

Approvals for marine applications		
		
Approval	Standard	Certificate Name
BV Bureau Veritas S.A.	Rules for class. of Steel Ships	40179_B0
DNV DNV Germany GmbH	DNV-CG-0339,Aug.2021	TAA00001D1

Approvals for hazardous areas		
		
Approval	Standard	Certificate Name
CCC CNEX	CNCA-C23-01	2020312310000210 (Ex ec IIC T4 Gc)
IECEX TUEV Nord Cert GmbH	-	IECEX TUN14.0030X
UKEx WAGO GmbH & Co. KG	EN 60079-0	WAGO22UKEX004X
UL Underwriters Laboratories Inc. (HAZARDOUS LOCATIONS)	ANSI/ISA 12.12.01	E198726



Downloads

Environmental Product Compliance

Compliance Search			
Environmental Product Compliance 857-810			

Documentation

Bid Text			
857-810	19.02.2019	xml 5.73 KB	
857-810	20.02.2019	docx 17.11 KB	

Instruction Leaflet			
CCC Ex (Additional information)	26.04.2023	pdf 140.99 KB	
Messumformer und Trennverstärker		pdf 2348.53 KB	

CAD/CAE-Data

CAD data	
2D/3D Models 857-810	

CAE data	
EPLAN Data Portal 857-810	
WSCAD Universe 857-810	
ZUKEN Portal 857-810	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Installation

1.1.1.1 Mounting accessories



[Item No.: 249-117](#)
Screwless end stop; 10 mm wide; for DIN-rail 35 x 15 and 35 x 7.5; gray



[Item No.: 249-197](#)
Screwless end stop; 14 mm wide; for DIN-rail 35 x 15 and 35 x 7.5; gray



[Item No.: 249-116](#)
Screwless end stop; 6 mm wide; for DIN-rail 35 x 15 and 35 x 7.5; gray

1.1.2 Interface module

1.1.2.1 Interface adapters



[Item No.: 857-980](#)
Interface adapter; 16-pole; analog



1.1.3 Jumper

1.1.3.1 Jumper

 Item No.: 281-482 Jumper; 2-way; insulated; gray	 Item No.: 859-410/000-006 Jumper; for jumper slot; 10-way; insulated; blue	 Item No.: 859-410 Jumper; for jumper slot; 10-way; insulated; light gray	 Item No.: 859-410/000-005 Jumper; for jumper slot; 10-way; insulated; red
 Item No.: 859-410/000-029 Jumper; for jumper slot; 10-way; insulated; yellow	 Item No.: 859-402/000-006 Jumper; for jumper slot; 2-way; insulated; blue	 Item No.: 859-402 Jumper; for jumper slot; 2-way; insulated; light gray	 Item No.: 859-402/000-005 Jumper; for jumper slot; 2-way; insulated; red
 Item No.: 859-402/000-029 Jumper; for jumper slot; 2-way; insulated; yellow	 Item No.: 859-403/000-006 Jumper; for jumper slot; 3-way; insulated; blue	 Item No.: 859-403 Jumper; for jumper slot; 3-way; insulated; light gray	 Item No.: 859-403/000-005 Jumper; for jumper slot; 3-way; insulated; red
 Item No.: 859-403/000-029 Jumper; for jumper slot; 3-way; insulated; yellow	 Item No.: 859-404/000-006 Jumper; for jumper slot; 4-way; insulated; blue	 Item No.: 859-404 Jumper; for jumper slot; 4-way; insulated; light gray	 Item No.: 859-404/000-005 Jumper; for jumper slot; 4-way; insulated; red
 Item No.: 859-404/000-029 Jumper; for jumper slot; 4-way; insulated; yellow	 Item No.: 859-405/000-006 Jumper; for jumper slot; 5-way; insulated; blue	 Item No.: 859-405 Jumper; for jumper slot; 5-way; insulated; light gray	 Item No.: 859-405/000-005 Jumper; for jumper slot; 5-way; insulated; red
 Item No.: 859-405/000-029 Jumper; for jumper slot; 5-way; insulated; yellow	 Item No.: 859-406/000-006 Jumper; for jumper slot; 6-way; insulated; blue	 Item No.: 859-406 Jumper; for jumper slot; 6-way; insulated; light gray	 Item No.: 859-406/000-005 Jumper; for jumper slot; 6-way; insulated; red
 Item No.: 859-406/000-029 Jumper; for jumper slot; 6-way; insulated; yellow	 Item No.: 859-407/000-006 Jumper; for jumper slot; 7-way; insulated; blue	 Item No.: 859-407 Jumper; for jumper slot; 7-way; insulated; light gray	 Item No.: 859-407/000-005 Jumper; for jumper slot; 7-way; insulated; red
 Item No.: 859-407/000-029 Jumper; for jumper slot; 7-way; insulated; yellow	 Item No.: 859-408/000-006 Jumper; for jumper slot; 8-way; insulated; blue	 Item No.: 859-408 Jumper; for jumper slot; 8-way; insulated; light gray	 Item No.: 859-408/000-005 Jumper; for jumper slot; 8-way; insulated; red
 Item No.: 859-408/000-029 Jumper; for jumper slot; 8-way; insulated; yellow	 Item No.: 859-409/000-006 Jumper; for jumper slot; 9-way; insulated; blue	 Item No.: 859-409 Jumper; for jumper slot; 9-way; insulated; light gray	 Item No.: 859-409/000-005 Jumper; for jumper slot; 9-way; insulated; red
 Item No.: 859-409/000-029 Jumper; for jumper slot; 9-way; insulated; yellow			



1.1.4 Marking

1.1.4.1 Marker



Item No.: 793-5501
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 793-502
WMB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-566
WMB marking card; as card; MARKED; 1 ... 50 (2x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-503
WMB marking card; as card; MARKED; 11 ... 20 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-504
WMB marking card; as card; MARKED; 21 ... 30 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-505
WMB marking card; as card; MARKED; 31 ... 40 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-506
WMB marking card; as card; MARKED; 41 ... 50 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-501
WMB marking card; as card; not stretchable; plain; snap-on type; white



Item No.: 2009-115
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.4.2 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

1.1.5 Power supply

1.1.5.1 Power supply



Item No.: 787-2852
Switched-mode power supply; 1-phase; 24 VDC output voltage; 1 A output current

1.1.6 Terminal blocks

1.1.6.1 Supply module



Item No.: 857-979
Supply and through module

1.1.6.2 Through terminal block



Item No.: 857-979
Supply and through module



1.1.7 Tool


1.1.7.1 Operating tool



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured


Installation Notes

Configuring



Configuration via DIP switch

Commoning



Commoning, not discrete wiring – Same outline allows use of a single in-line, push-in jumper.