

TDK-Lambda CUS600M and CUS600M1 Series

3 x 5" 600W AC-DC Power Supplies

<https://product.tdk.com/en/power/cus-m>
www.emea.lambda.tdk.com/cus600m



Medical



Industrial



Test



LED



COMM



Broadcast



The compact CUS600M is packaged in the industry standard 3x5" footprint and can deliver 600W with forced air or 400W with a 600W peak power with convection cooling. With Medical & ITE certifications, the unit can be used in both Class I & Class II (no ground wire) applications⁽¹⁾. A 5V 2A standby voltage, remote on/off, remote sense and a Power Good signal is standard on the CUS600M. Options include an internal fan and output adjustment. The CUS600M1 models offer a reduced feature set for cost optimization.

Features	Benefits
• 400W (600W Peak) Convection Cooled	• Quiet Operation
• 600W with Forced Air	• Can Utilize System Airflow or Integrated Fan
• Medical Certifications (2 x MOPP)	• Suitable for B and BF Type Medical Equipment
• Class B Conducted and Radiated EMI	• Easier System EMC Compliance
• Suitable for Class I and Class II installations ⁽¹⁾	• Flexible Utilization
• Compact 3 x 5 x 1.46" Size	• Space Saving in End Equipment
• Enclosure & Other Options	• Versatile Application

Model Selector							
Model	Nominal Output Voltage (V)	Output Adjustment (V) (Specify /ADJ option suffix*) ⁽²⁾	Maximum Current Convection (A)	Maximum Current Forced Air (A)	Peak Current (A)	Maximum Power Convection (W)	Maximum Power Forced Air (W)
CUS600M-12	12	11.7 - 12.9	33.4	50.0	50.0	400.8	600.0
CUS600M-19	19	18.5 - 20.5	21.1	31.6	31.6	400.9	600.4
CUS600M-24	24	23.4 - 25.9	16.7	25.0	25.0	400.8	600.0
CUS600M-28	28	27.3 - 30.2	14.3	21.5	21.5	400.4	602.0
CUS600M-32	32	31.2 - 34.5	12.5	18.8	18.8	400.0	601.6
CUS600M-36	36	35.1 - 38.8	11.1	16.7	16.7	399.6	601.2
CUS600M-48	48	46.8 - 51.8	8.4	12.6	12.6	403.2	604.8

CUS600M-			12	/	EF
Features	CUS600M-	CUS600M1-	Output voltage 12, 19, 24, 28, 32, 36, 48		blank Open frame construction /EF Enclosed with end fan (exhaust air)* /ADJ Output adjustment potentiometer**
Standby Voltage	Yes	Not Available			
Remote On/Off					
Remote Sense					
Power Good Signal					

* /EF model has /ADJ included (CUS600M only)

Other options are available, please contact sales

Specifications		
Model		CUS600M
Input		
Input Voltage Range (Operating)	Vac	85 - 265 (See derating curves)
Nominal Input Voltage Range	Vac	100 - 240 (Note: Safety certified for 90-264Vac only)
Input Frequency	Hz	47 - 63
Input Current (110/230Vac)	A	< 6.0 / 3.0 (600W)
Inrush Current at 230Vac (typ) (Cold Start)	A	<50
Leakage Current	uA	<200uA at 265Vac 60Hz
Touch Current (Enclosure Leakage)	uA	<100
Power Factor (115/230Vac)	-	0.99 / 0.95
Harmonic Compliance	-	Meets IEC61000-3-2 Class A
No Load Power Consumption	W	<0.5W at 230Vac (Remote off and no load on 5Vsb)
Hold Up Time (typ) at 115Vac Input	ms	>22ms 400W load, >14ms 600W load
Efficiency	-	Up to 96%
Conducted & Radiated EMI (Class I only ⁽¹⁾)	-	EN55032/EN55011-B (See installation / instruction manual for conditions)
Immunity (Class I only ⁽¹⁾)	-	Compliant with EN60601-1-2:2015 (Ed4), see immunity table
Insulation Class	-	Construction suitable for Class I or Class II installation ⁽¹⁾
Safety Certifications and Markings	-	IEC/EN/UL/CSA62368-1 and IEC/EN/ES/CSA60601-1, CQC ⁽³⁾ , CE Mark and UKCA Mark

Immunity				
Test	Standard	Test Level	Criteria	Notes ⁽¹⁾ (the power stated below is total power (main power + fan output))
ESD	EN61000-4-2	4	A	-
Radiated Susceptibility	EN61000-4-3	3	A	Includes proximity field requirements of EN60601-1-2:2015
Electrical Fast Transient Burst	EN61000-4-4	4	A	(AC Port, 5kHz and 100kHz)
Surge	EN61000-4-5	3	A	-
Conducted Susceptibility	EN61000-4-6	3	A	-
Magnetic fields	EN61000-4-8	4	A	-
Voltage Dips and Input Interruptions	EN61000-4-11 Class 3 Industrial, incl EN55024 (100Vac)	0% for 1/2 cycle	A	-
		0% for 1 cycle	A/B	A up to 330W, B above 330W
		40% for 10/12 cycles	A/B	A up to 210W, B above 210W
		70% for 25/30 cycles	A/B	A up to 500W, B above 500W
		80% for 250/300 cycles	A/B	A up to 570W, B above 570W
		0% for 250/300 cycles	B	-
	EN61000-4-11 Class 3 Industrial, incl EN55024 (240Vac)	0% for 1/2 cycle	A	-
		0% for 1 cycle	A/B	A up to 330W, B above 330W
		40% for 10/12 cycles	A/B	A up to 570W, B above 570W
		70% for 25/30 cycles	A	-
		80% for 250/300 cycles	A	-
		0% for 250/300 cycles	B	-
	EN60601-1-2:2015 (100Vac)	0% for 1/2 cycle	A	Customer to consider essential performance of end equipment
		0% for 1 cycle	A/B	A up to 330W, B above 330W
		70% for 25/30 cycles	A/B	A up to 500W, B above 500W
		0% for 250/300 cycles	B	-
	EN60601-1-2:2015 (240Vac)	0% for 1/2 cycle	A	Customer to consider essential performance of end equipment
		0% for 1 cycle	A/B	A up to 330W, B above 330W
		70% for 25/30 cycles	A	-
		0% for 250/300 cycles	B	-
SEMI F47 Line Dip	SEMI F47	-	-	At input voltages > 200Vac

Notes:

See website for detailed specifications, test methods and installation manual

Specification parameters apply at 25°C ambient temperature unless otherwise stated.

(1) Class II operation may require additional EMC filtering, contact factory for assistance.

(2) Not available on the CUS600M1 models, see model selector

(3) CUS600M1-24/CQC model, minimum orders apply, contact sales for other model configurations

Specifications		
Model		CUS600M
Output		
Line Regulation	%	0.5% (85 - 265Vac)
Load Regulation	%	1% (0 - 100% load)
External Load Capacitance	uF	12-19V: 10,000, 24V: 8,000, 28V: 5,000, 32-36V: 4,000, 48V: 3,000
Ripple & Noise	mV	12V: 240mV, 19V - 28V: 360mV, 32V - 48V: 480mV
Temperature Coefficient	%/°C	±0.02%/°C
Minimum Load	-	No minimum load required
Overcurrent Protection	%	>105%. Hiccup mode, automatic recovery
Overvoltage Protection	V	12V: 13.8-16.2, 19V: 21.8-25.7, 24V: 27.6-32.4, 28V: 32.2-37.8, 32V: 36.8-43.2, 36V: 41.4-48.6, 48V: 55.2-64.8 Latching (unit shutdown), cycle AC input to reset
Overtemperature Protection	-	Latching (unit shutdown), cycle AC input to reset
Remote Sense	-	0.5V total compensation ⁽²⁾
Remote On/Off	-	Opto-isolated. Inhibit: Low = ON, High = OFF ⁽²⁾
Power Good	-	Combined AC Fail and DC OK opto isolated signal ⁽²⁾
Standby Voltage	-	Open frame version: 5V 2A, /EF version 5V 1.5A ⁽²⁾
Parallel Operation	-	Not possible
Environmental		
Operating Temperature	°C	-20°C to +70°C, see derating curves below
Storage Temperature	°C	-40°C to +85°C
Operating Humidity (non condensing)	%RH	10 - 95%RH
Cooling	-	Convection cooling or forced air (2.7m/s). (/EF version, air exits from fan end)
Altitude	m	5,000m. Operating, transportation and storage
Withstand Voltage (For 1 minute)	Vac	Input to Ground 2kVAC (1xMOPP), Input to Output 4kVAC (2xMOPP), Output to Ground 1.5kVAC (1xMOPP)
Isolation Resistance	MΩ	>100MΩ at 25°C, 70%RH Output - FG 500VDC
Vibration (Non Operating)	-	10-55Hz (1 min sweep). Maximum 19.6m/s ² ; x, y, z for 1 hour each
Shock	-	<196m/s ²
Other		
Weight (Typ)	g	Open frame: 470, /EF: 790
Size (LxWxH)	mm	Open frame: 127 x 76.2 x 37, /EF: 157 x 85 x 42.5
Size (LxWxH)	Inches	Open frame: 5 x 3 x 1.46, /EF: 6.18 x 3.35 x 1.67
Connectors	-	Input: JST VHR-5N, Output: M4 screws, Standby: JST XHP-2, Signals: JST PHDR-08VS
Warranty	yrs	5

Notes:

See website for detailed specifications, test methods and installation manual


Specification parameters apply at 25°C ambient temperature unless otherwise stated.

(1) Class II operation may require additional EMC filtering, contact factory for assistance.


(2) Not available on the CUS600M1 models, see model selector

(3) CUS600M1-24/CQC model, minimum orders apply, contact sales for other model configurations

Mounting Orientation




Airflow Direction



Convection Cooling CUS600M-12

(Zero load on Standby Voltage. Wide range input. Additional derating applies below 115Vac input)


Ta (°C)	Mounting A	Mounting B C	Mounting D	Mounting E
	LOAD (%)	LOAD (%)	LOAD (%)	LOAD (%)
-20 - +35	100	100	90	90
40	100	93.3	81.4	82.9
50	83.3	80	64.3	68.6
60	66.7	60	47.1	54.3
70	50	40	30	40



Convection Cooling CUS600M-19 to -48

(Zero load on the Standby Voltage output. Wide range input. Additional derating applies below 115Vac input)


Ta (°C)	Mounting A	Mounting B C E	Mounting D
	LOAD (%)	LOAD (%)	LOAD (%)
-20 - +35	100	100	90
40	100	93.3	81.4
50	83.3	80	64.3
60	66.7	60	47.1
70	50	40	30



Convection Cooling (All models)

(Loading applied on the Standby Voltage output. Wide range input. Additional derating applies below 115Vac input)

Ta (°C)	Mounting A	Mounting B C	Mounting D E
	LOAD (%)	LOAD (%)	LOAD (%)
-20 - +30	100	100	90
35	100	95	82.5
40	93.3	90	75
50	80	80	60
60	60	60	45
70	40	40	30




Convection Cooling CUS600M-12

(Loading applied on the Standby Voltage output. 176 - 265Vac input. Additional derating applies below 115Vac input)

MODEL: CUS600M-12


Ta (°C)	Mounting A B D	Mounting C	Mounting E
	LOAD (%)	LOAD (%)	LOAD (%)
-20 - +30	100	100	100
40	100	100	82.5
50	80	83.3	65
60	60	66.7	47.5
70	40	50	30



Convection Cooling CUS600M-19 to -48V

(Loading applied on the Standby Voltage output. 176 - 265Vac input. Additional derating applies below 115Vac input)


Ta (°C)	Mounting A B D	Mounting C	Mounting E
	LOAD (%)	LOAD (%)	LOAD (%)
-20 - +30	100	100	100
40	100	100	82.5
45	90	100	73.8
50	80	90	65
60	60	70	47.5
70	40	50	30



Forced Air Cooling CUS600M-12 (2.7m/s)

(Loading applied on the Standby Voltage output. Wide range input. Additional derating applies below 115Vac input)


Ta (°C)	Direction A	Direction B	Direction C	Direction D
	LOAD (%)	LOAD (%)	LOAD (%)	LOAD (%)
-20 - +25	100	100	100	100
35	93.3	100	100	100
40	90	94.3	100	100
45	85	90.2	100	100
50	80	86.2	100	94
55	75	82.1	100	88
60	70	78	90	82
70	60	70	70	70




Forced Air Cooling CUS600M-19 to -48 (2.7m/s)

(Loading applied on the Standby Voltage output. Wide range input. Additional derating applies below 115Vac input)

Ta (°C)	Direction A D	Direction B	Direction C
	LOAD (%)	LOAD (%)	LOAD (%)
-20 - +35	100	100	100
40	94.3	94.3	100
50	82.8	86.2	100
55	77.1	82.1	100
60	71.4	78	90
70	60	70	70




CUS600M-xx/EF (End Fan)




Derating versus Input Voltage

(All models, all conditions)




Mechanical Specification

Outline Drawing CUS600M Open Frame Unit




Mechanical Specification

Outline Drawing CUS600M1 Open Frame Unit



Outline Drawing CUS600M/EF (End Fan)



**TDK-Lambda France SAS**

Tel: +33 1 60 12 71 65
 ttf.fr-powersolutions@tdk.com
 www.emea.lambda.tdk.com/fr

**TDK-Lambda Americas**

Tel: +1 800-LAMBDA-4 or 1-800-526-2324
 tla.powersolutions@tdk.com
 www.us.lambda.tdk.com

**Italy Sales Office**

Tel: +39 02 61 29 38 63
 ttf.it-powersolutions@tdk.com
 www.emea.lambda.tdk.com/it

**TDK Electronics do Brasil Ltda**

Tel: +55 11 3289-9599
 sales.br@tdk-electronics.tdk.com
 www.tdk-electronics.tdk.com/en

**Netherlands**

ttf.nl-powersolutions@tdk.com
 www.emea.lambda.tdk.com/nl

**TDK-Lambda Corporation**

Tel: +81-3-6778-1113
 www.jp.lambda.tdk.com

**TDK-Lambda Europe GmbH**

Tel: +49 7841 666 0
 tlg.powersolutions@tdk.com
 www.emea.lambda.tdk.com/de

**TDK-Lambda (China) Electronics Co. Ltd.**

Tel: +86 21 6485-0777
 tlc.powersolutions@tdk.com
 www.lambda.tdk.com.cn

**Austria Sales Office**

Tel: +43 2256 655 84
 tlg.at-powersolutions@tdk.com
 www.emea.lambda.tdk.com/at

**TDK-Lambda Singapore Pte Ltd.**

Tel: +65 6251 7211
 tfs.marketing@tdk.com
 www.sg.lambda.tdk.com

**Switzerland Sales Office**

Tel: +41 44 850 53 53
 tlg.ch-powersolutions@tdk.com
 www.emea.lambda.tdk.com/ch

**TDK India Private Limited, Power Supply Division**

Tel: +91 80 4039-0660
 mathew.philip@tdk.com
 www.sg.lambda.tdk.com

**TDK-Lambda Europe GmbH**

Tel: +45 3222 8086
 tlg.dk-powersolutions@tdk.com
 www.emea.lambda.tdk.com/dk

**TDK-Lambda UK Ltd.**

Tel: +44 (0) 12 71 85 66 66
 tlu.powersolutions@tdk.com
 www.emea.lambda.tdk.com/uk

**TDK-Lambda Israel Ltd.**

Tel: +972 3 902 4333
 tli.powersolutions@tdk.com
 www.emea.lambda.tdk.com/il-en

