

RS-232 2kV Isolated Repeater

Model 232OPDR



PRODUCT FEATURES

- Extends RS-232 data another 15.2 m (50 ft)
- 2,000V optical isolation on data lines
- -40 to +80 °C wide operating temperature
- DIN rail mount, IP30 case (panel mount option)
- UL Recognized, NEMA TS2
- 10 - 30 VDC power, terminal block connector

Model 232OPDR is a DIN rail mountable RS-232 optical isolator and repeater. It provides 2,000 V isolation for four RS-232 signal lines (two in each direction). Isolation protects computer equipment from ground loops and induced currents caused by lightning or heavy electrical loads. It also functions as a repeater to extend RS-232 signals another 15.2 meters (50 ft).

Model 232OPDR has four LEDs to indicate data flow and one LED to indicate power. It can support two data pairs or one data pair plus control signals in both directions. Connections are made to a terminal block.

ORDERING INFORMATION

MODEL NUMBER	DESCRIPTION
232OPDR	RS-232 2kV Isolated Repeater

ACCESSORIES - sold separately

- MDR-20-24 - DIN rail mount power supply 24VDC, 1.0 A output power
- MDR-40-24 - DIN rail mount power supply 24VDC, 1.7 A output power
- DRPM25 - 35mm DIN rail to panel mount bracket, 25mm wide
- EK-CLIP-MPC - DIN rail clip for enclosure

All product specifications are subject to change without notice.
232OPDR_2118ds

RS-232 2kV Isolated Repeater

Model 232OPDR



SPECIFICATIONS

RS-232	
Connector	Terminal Block
Signals	4 signal lines in each direction. Protected ground on isolated side.
ISOLATION	
Method	Optical
Rating	2,000 V
POWER	
Connector	Terminal block
Voltage	10 to 30 VDC
Power Consumption	1.2 W
Source	External
TERMINAL BLOCKS	
Wire Size	24 to 14 AWG
Torque	4 kgf-cm
LED INDICATORS	
Data LEDs (RED)	Data LED for each side of isolator Flashes when data transmitted
Power LED (RED)	ON when power applied

SPECIFICATIONS

ENCLOSURE	
Material	Plastic
IP Rating	IP30
Dimensions	2.5 x 7.9 x 9.5 cm (1.0 x 3.1 x 3.7 in)
Mounting	35 mm DIN (panel mount adapter available)
ENVIRONMENTAL	
Operating Temperature	-40 to +80 °C (-40 to +176 °F)
Storage Temperature	-40 to +85 °C (-40 to +185 °F)
Operating Humidity	0 to 95% Non-condensing
Meantime Before Failure (MTBF)	244689 hours
MTBF Calculation Method	MIL217F Parts Count Reliability
APPROVALS, DIRECTIVES, STANDARDS	
CE, FCC, NEMA TS2, UL508 cULus Recognized, File E222870	

MECHANICAL

Units = cm / in

