
Rev	AWO #	Description	Date	Appr
-		RELEASED	4/15/19	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

Positions: 02 thru 12
A = .224 [5.70] x No. of Spaces + .250 [6.35]
B = .224 [5.70] x No. of Spaces

SPECIFICATIONS:
Material:
Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
Insulator color: Black
Contact: Brass, Matte Tin plated
Electrical:
Voltage rating: 600 VAC/DC
Current rating: 23 A AC/DC
Contact resistance: 2 mohms max.
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding voltage: 2,200 VAC for 1 minute
Temperature Rating:
-40°C to +105°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	OW	4/15/19
CHECKED	DH	4/15/19
APPROVED		

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.224 [5.70] RIGHT ANGLE PCB HEADER WITH PEGS

SIZE	PART NO.	REV.
X	DMB-LF-XX-A-H-MT-A-HT-V0	-

REF: S00123T | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.