



Part Number : [565790519](#)
Product Description : Mini USB, AB-Receptacle,
Right-Angle, Through Hole Solder Tails and Shell Tabs,
Lead-Free
Series Number : 56579
Status : Not Recommended For New Design
Product Category : I/O Connectors

Documents and Resources

Drawings

[565790519 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[SPK-56579-001-001.pdf](#)

[PS-56579-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	I/O Connectors
Series	56579
Description	Mini USB, AB-Receptacle, Right-Angle, Through Hole Solder Tails and Shell Tabs, Lead-Free
Application	Wire-to-Board
Component Type	Receptacle
Product Name	USB
Standard	USB 2.0
Type	Mini-AB
UPC	822348297177

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.0A
Shielded	Yes
Shield Type	Full Shield

Voltage - Maximum	30V AC (RMS)/DC
-------------------	-----------------

Physical

Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Gray
Gender	Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA), Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Mounting Style	Top-Mount
Net Weight	584.300/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	0.80mm
PC Tail Length	1.80mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20° to +85°C
Termination Interface Style	Through Hole
Waterproof / Dustproof	No
Wire Size (AWG)	N/A