

**Part Number :** [190080029](#)

**Product Description :** Flag Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm<sup>2</sup>) Wire, Metal Strip, Tab 4.75 x 0.81mm

**Series Number :** 19008

**Status :** Active

**Product Category :** Quick Disconnects

**Engineering Part Number :** BBZ-1148-032



---

## Documents and Resources

### Drawings

[190080029\\_sd.pdf](#)

[PK-19009-001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-19902-005-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Quick Disconnects
Series	19008
Description	Flag Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm <sup>2</sup> ) Wire, Metal Strip, Tab 4.75 x 0.81mm
Product Name	Krimptite
Type	Flag Terminal
UPC	800755046670

### Agency

CSA	LR18689
UL	E79133

### Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

### Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	No

Insulation	None
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.676/g
Orientation	Flag
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	4.75mm
Temperature Range - Operating	Per Wire Specification
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm <sup>2</sup>	1.30-2.00

---

## Application Tooling

### Global

Description	Part Number
Mini-Mac Rear Feed Applicator	<u>638027600</u>

---

This document was generated on May 20, 2026