

M12-S-PPI-CC-IDC-4P-ACOD-F-STR



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 111 2415
Specification	M12-S-PPI-CC-IDC-4P-ACOD-F-STR
HARTING eCatalogue	https://harting.com/21031112415

Identification

Category	Connectors
Series	Circular connectors M12
Identification	PushPull
Element	Cable connector
Specification	Straight

Version

Termination method	HARAX [®] connection technology
Gender	Female
Shielding	Unshielded
Number of contacts	4
Coding	A-coding
Locking type	PushPull (outer)

Technical characteristics

Conductor cross-section	0.14 ... 0.34 mm ²
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Wire outer diameter	≤1.6 mm
Rated current	4 A
Rated voltage	48 V AC 60 V DC
Rated impulse voltage	1.5 kV
Pollution degree	3



Pushing Performance
Since 1945

Technical characteristics

Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	2.9 ... 5.1 mm
Isolation group	I ($600 \leq \text{CTI}$)

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-2-101 IEC 61076-2-010
----------------	------------------------------------

Commercial data

Packaging size	1
Net weight	17 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140226777
eCl@ss	27440116 Circular connector (for field assembly)
ETIM	EC002635



Pushing Performance
Since 1945

Commercial data

UNSPSC 24.0

39121413
