





PART NUMBER	SIZE	L	M	A	FACTORY NUMBER
P-2404H-SB	4	1.938 [49.23]	1.500 [38.10]	1.250 [31.75]	703 03 04 005
P-2406H-SB	6	2.375 [60.33]	1.938 [49.23]	1.688 [42.88]	703 03 06 005
P-2408H-SB	8	2.813 [71.45]	2.375 [60.33]	2.125 [53.98]	703 03 08 005
P-2410H-SB	10	3.250 [82.55]	2.813 [71.45]	2.563 [65.10]	703 03 10 005
P-2412H-SB	12	3.688 [93.68]	3.250 [82.55]	3.000 [76.20]	703 03 12 005

DRAWING REVISIONS			
REV	DOCUMENT	APP	DATE
I	DO 06-1068		



NOTES:

1. SPECIFICATIONS:

ELECTRICAL:
 OPERATING VOLTAGE: 250 VAC RMS
 CURRENT RATING: 15 AMPS
 CURRENT RESISTANCE: 1.0 MIILOHMS MAXIMUM

INSULATOR: MOLDED MONBLOCK, GENERAL PURPOSE PHENOLIC, BLACK

CONTACT: BRASS, MATTE TIN

SCREW: STEEL, ZINC WITH CLEAR TRIVALENT CHROME

BRACKET: BLACK CRINKLE

ENVIRONMENTAL:
OPERATING TEMPERATURE: UP TO +105°C

TERMINATION: SOLDER

2. DIMENSIONS IN [] ARE MILLIMETERS

3. ALL DIMENSIONS ARE REFERENCE

RoHS COMPLIANT

UNITS	ENGLISH INCHES		PRO/E	Cinch	JIMENEZ 1700 FINLEY RD. LOMBARD, IL. 60148	
DO NOT SCALE DRAWING		DRAWN BY JIMENEZ	DATE 7/31/06	TITLE PLUG AND SHALLOW BRACKET ASSEMBLY		
UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS ARE IN INCHES FILLET/RADIUS .02 MAX TOLERANCES .X ± .1 .XX ± .01 .XXX ± .005 ANGULAR ± .5°		DESIGN ENGINEER A. BALI	7/31/06	MATERIAL CONTROL SPEC NUMBER 06-1068		
		DESIGN ENGINEERING MGR.		MATERIAL SPEC NUMBER	FINISH	PROJECT NUMBER C14789-2
		MFG. ENGINEERING		CAD FILE NUMBER P2404HSB	DRAWING NUMBER P-2404H-SB	
THIS DOCUMENT IS THE PROPERTY OF CINCH. NEITHER THIS DOCUMENT NOR ANY OF THE INFORMATION CONTAINED IN IT MAY BE DUPLICATED OR DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF CINCH.		QUALITY ASSURANCE	CAGE IDENT NO. SIZE 71785 B	SCALE 1.000	SHEET 1 OF 1	