


DRAWING REVISIONS (RELEASE DATE ON FILE)			
REV	DOCUMENT	APP	APPROVAL DATE
D	PER CO# 839	V.R.	02/18/10






SECONDARY LOCK SHIPPED
IN PRE-STAGED POSITION



REAR VIEW



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES.
2. FOR WIRE SIZE APPLICATION, CONSULT FACTORY.
3. FEMALE TERMINAL ORDERED SEPARATELY: 425 00 00 873/872.
4. MATES WITH CINCH HEADER CONNECTOR (CONSULT FACTORY).
5. SEAL PLUG ORDERED SEPARATELY: 581 00 00 011.
6. TOLERANCES UNLESS OTHERWISE SPECIFIED:
   .X ±0.5
   .XX ±0.25
7. SEALING RANGE FOR WIRE INSULATION DIA.;
   MAX 2.64MM (.104"), MIN 1.96MM (.077").
8. A TRIANGLE ▲ INDICATES CRITICAL FUNCTION DIMENSION.
9. IF TIE-WRAP DRESSING CONDUCTORS, CINCH RECOMMENDS A SPACING
   OF NO LESS THAN 2 INCHES BEHIND THE BACK PLATE.

UNITS: METRIC	PRO/E	CINCH	MODELED BY: 1700 FINLEY RD LOMBARD, IL. 60148
DO NOT SCALE DRAWING	DESIGN ENGINEER: A. CAINES	DATE: 4/25/00	TITLE: 18 POSITION SOCKET CONNECTOR
APPROVALS ON FILE	MATERIAL		CONTROL SPEC NUMBER
	MATERIAL SPEC NUMBER	FINISH	PROJECT NUMBER: A14243
	CAD FILE NUMBER: 5810118024		DRAWING NUMBER: 5810118024S
	CAGE IDENT NO.: 71785	SIZE: B	SCALE: 3:2 — SHEET 1 OF 1

CONFIDENTIAL
THIS DOCUMENT IS THE PROPERTY OF CINCH. NEITHER THIS DOCUMENT NOR ANY OF THE INFORMATION CONTAINED IN IT MAY BE DUPLICATED OR DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF CINCH.
©COPYRIGHT 2010 CINCH

Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.