



3M Electrical

Solutions for Electrical

- Electrical Construction & Maintenance
- Electrical and Electronic OEM
- Utilities
 - Mining
 - Field Training
 - Oil & Gas
- Heat Tracing
 - Heat Tracing Design Software Registration
- Job Box

Product and Services

- Products
- Where to Buy
- Request Product Information
- Shelf Life & Storage Conditions

Resources

- Industry Standards & Compliance
- Literature Selector

News & Events

- Press Releases
- Industry Links

Support

- Contact Us
- Training

Heat Tracing

Product Catalog for 3M Mining > 3M Electronics Manufacturing > 3M™ Tapes > 3M™ Noise & Vibration Control > 3M™ Foam Tapes > 3M™ Vinyl Foam Tape 4508 >

3M™ Vinyl Foam Tape 4508 Black, 3/8 in x 36 yd, 24 per case

[Printer-friendly format](#)

3M™ Vinyl Foam Tape 4508 is a vinyl, conformable, single-coated, closed-cell foam tape. 1/8 in thick.

3M Id : 70-0024-6002-3
GTIN(UPC/EAN) : 0 00 21200 03311 7

Additional Information

Bonds and seals to a variety of surfaces.

Learn More . . .

- [Packaging Data](#)
- [MSDS \(Canada - en\)](#)

Characteristics

Adhesive Material	Acrylic
Adhesive Type	3M Adhesive 430
Backing Material	Foam
Carrier Material	Vinyl
Color	Black
Density	20 Pound Per Cubic Foot
Diameter	14.9 Inch
Double Sided Adhesive	No
Length	36 Linear Yard
Liner Color	White
Liner Thickness	3 Milli-inch (mil)
Liner Type	Paper
Product Form	Roll
Shelf Life	18 Month
Tape Type	Single Coated
Temperature Resistance - Initial	250 Degree Fahrenheit
Temperature Resistance - Long Term	150 Degree Fahrenheit
Thickness	125 Milli-inch (mil)
Trademark Name 1	3M
Units per Case	24
Width	3/8 Inch

Quick Clicks

- Where to Buy
- Product Selectors
- Contact Us
- ☒ RoHS Compliance Product Look Up
- ☐ Material Safety Data Sheets

FREE
Download your
copy of the TTS™
Trace Design
Software

Where to Buy
and/or
Request More
Information

Related Links

- [Sustainability](#)
- [3M RoHS Specification](#) (PDF 46K)
- [RoHS Directive](#)
- [Request more RoHS](#)
- [Compliance Information](#)
- [WEEE Initiative](#)
- [WEEE Legislative Summary](#)

