





Mating Height Draw.



Pos	A	B	C	Pos	A	B	C
4	7.00	3.81	5.60	16	22.24	19.05	20.84
6	9.54	6.35	8.14	18	24.78	21.59	23.38
8	12.08	8.89	10.68	20	27.32	24.13	25.92
10	14.62	11.43	13.22	22	29.86	26.67	28.46
12	17.16	13.97	15.76	24	32.40	29.21	31.00
14	19.70	16.51	18.30	26	34.94	31.75	33.54

Specifications:

Current rating:1.5A AC,DC

Voltage rating:230V AC, DC

Contact resistance:20m ohm. Max.

Insulation resistance:1000M ohm. Min.

Withstanding voltage:AC 500V AC/minute

Operating temperature range:-40°C ~ +105°C

Materials:


Insulator:High Temp. Plastic (UL94V-0)

Contact material:Phosphor Bronze

Finish:Tin Plated

How to Order

TMM-X-X-XX-X	
Type	Packaging
1-IDC Male	1 - Tape & Reel with vacuum cap
2-IDC Plug	2 - Tube
3-DIP Male Straight	3 - Bag
4-DIP Female Straight	4- Tape & Reel without vacuum cap
5-DIP Female R/A	Number of Positions
6-SMT Female Straight	04, 06, 08, 10, 12, 14, 16, 18, 20, 22, 24 or 26
Locking System	
0-without lock	
L-with lock	



PCB Layout



TOLERANCE (mm)	APPROVALS	DATE	TITLE		AMPHENOL	
X. ±0.3	DRAWN Stephane	2009/10/07	TMM Series R/A Dip Female		Amphenol European Design Center	
X.X ±0.2	CHECKED Rob	2009/10/07			Scale N.A. Sheet 1 of 1	
X.XX ±0.15	APPROVED Rob	2009/10/07			REV. D	
UNLESS OTHERWISE SPECIFIED	UNIT: mm	SIZE: A4	DRAWING N° TMM-5-0-XX-X			