

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006
© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST
J	

REVISIONS (変更)

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-10-007266	21APR2010	HMR	T.M







RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1


推奨基板取付穴寸法；コネクタ搭載面（非累積公差）
PC基板厚：1.0~1.6±0.1

4-1939261-□ : YELLOW (Y-KEY)
3-1939261-□ : YELLOW (X-KEY)
2-1939261-□ : NATURAL (Y-KEY)
1-1939261-□ : NATURAL (X-KEY)





20POS(X-KEY):
1-1939261-0(NATURAL)
3-1939261-0(YELLOW)



POS	n	KEY	A	B	C	PART NO (COLOR)
20	9	Y	22.5	26.0	27.6	4-1939261-0 (YELLOW)
20	9	X	22.5	26.0	27.6	3-1939261-0 (YELLOW)
20	9	Y	22.5	26.0	27.6	2-1939261-0 (NATURAL)
20	9	X	22.5	26.0	27.6	1-1939261-0 (NATURAL)
12	5	Y	12.5	16.0	17.6	4-1939261-6 (YELLOW)
12	5	X	12.5	16.0	17.6	3-1939261-6 (YELLOW)
12	5	Y	12.5	16.0	17.6	2-1939261-6 (NATURAL)
12	5	X	12.5	16.0	17.6	1-1939261-6 (NATURAL)
10	4	Y	10.0	13.5	15.1	4-1939261-5 (YELLOW)
10	4	X	10.0	13.5	15.1	3-1939261-5 (YELLOW)
10	4	Y	10.0	13.5	15.1	2-1939261-5 (NATURAL)
10	4	X	10.0	13.5	15.1	1-1939261-5 (NATURAL)
8	3	Y	7.5	11.0	12.6	4-1939261-4 (YELLOW)
8	3	X	7.5	11.0	12.6	3-1939261-4 (YELLOW)
8	3	Y	7.5	11.0	12.6	2-1939261-4 (NATURAL)
8	3	X	7.5	11.0	12.6	1-1939261-4 (NATURAL)
6	2	Y	5.0	8.5	10.1	4-1939261-3 (YELLOW)
6	2	X	5.0	8.5	10.1	3-1939261-3 (YELLOW)
6	2	Y	5.0	8.5	10.1	2-1939261-3 (NATURAL)
6	2	X	5.0	8.5	10.1	1-1939261-3 (NATURAL)
4	1	Y	2.5	6.0	7.6	4-1939261-2 (YELLOW)
4	1	X	2.5	6.0	7.6	3-1939261-2 (YELLOW)
4	1	Y	2.5	6.0	7.6	2-1939261-2 (NATURAL)
4	1	X	2.5	6.0	7.6	1-1939261-2 (NATURAL)

1. MATERIAL
HOUSING:GLASS FILED THERMO PLASTIC POLYESTER(94V-0)
COLOR:EXCLUDING BLACK
CONTACT:COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY

2. FINISH(ALL OVER):NICKEL PL. 1.27μmMIN

3. FINISH(CONTACT AREA):GOLD PL. 0.38μmMIN AFTER 2

4. FINISH(CONTACT TAIL):TIN PL. 2μmMIN AFTER 2

5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

6. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".

1. 材料
ハウジング：ガラス入り熱可塑性ポリエステル樹脂（94V-0）
色：黒以外
コンタクト：銅合金
リテンションレグ：錫めっき済銅合金

2. めっき-全面：ニッケル下地めっき1.27μm以上

3. めっき-接触部：2の上に金めっき0.38μm以上

4. めっき-コンタクト半田付部：2の上に錫めっき2μm以上

5. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。

6. Y KEY形状は、X KEY形状と左右対称

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位: 粍 mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
一般公差 ±0.3, ±3°
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
MATERIAL 材料
FINISH 仕上

DWN M.MAEBASHI 19APR2006
CHK T.KUDO 19APR2006
APVD D.MITSUGI 19APR2006
PRODUCT SPEC 製品規格 108-78268
APPLICATION SPEC 設計適用規格 114-5377
WEIGHT
CUSTOMER DRAWING

Tyco Electronics
Tyco Electronics Corporation
Kawasaki, Japan

NAME 名称
DYNAMIC D1200D 2.5mmPITCH
HDR ASSY, V-TYPE, COLOR
4-20POS

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A2	00779	C-1939261	

SCALE 尺度 5:1 SHEET 1 OF 3 REV B

1471-9 (2/09)


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006
© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION, ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST
J	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 3			




4POS(X-KEY):
1-1939261-2(NATURAL)
3-1939261-2(YELLOW)



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

推奨基板取付穴寸法：コネクタ搭載面（非累積公差）
PC基板厚：1.0~1.6±0.1

ONLY 4POS



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN M.MAEBASHI 19APR2006	Tyco Electronics Corporation Kawasaki, Japan
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	CHK T.KUDO 19APR2006	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY, V-TYPE, COLOR 4-20POS
		APVD D.MITSUGI 19APR2006	
		PRODUCT SPEC 108-78268	
		APPLICATION SPEC 114-5377	SIZE A2 / CAGE CODE 00779 / DRAWING NO C-1939261 / RESTRICTED TO
MATERIAL	FINISH	WEIGHT	SCALE 5:1 / SHEET 2 OF 3 / REV B
		CUSTOMER DRAWING	


Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006
© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION, ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST
J	


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 3			


























6POS(X-KEY):
1-1939261-3(NATURAL)
3-1939261-3(YELLOW)



8POS(X-KEY):
1-1939261-4(NATURAL)
3-1939261-4(YELLOW)



10POS(X-KEY):
1-1939261-5(NATURAL)
3-1939261-5(YELLOW)



12POS(X-KEY):
1-1939261-6(NATURAL)
3-1939261-6(YELLOW)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

FINISH

DWN M.MAEBASHI 19APR2006
CHK T.KUDO 19APR2006
APVD D.MITSUGI 19APR2006
PRODUCT SPEC 108-78268
APPLICATION SPEC 114-5377
WEIGHT

CUSTOMER DRAWING

Tyco Electronics
Tyco Electronics Corporation
Kawasaki, Japan

NAME DYNAMIC D1200 2.5mmPITCH HDR ASSY, V-TYPE, COLOR 4-20POS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1939261	

SCALE 5:1 SHEET 3 OF 3 REV B

Downloaded from Arrow.com.