


COAXIAL SURGE PROTECTOR DEVICE, Miniature GDT technology
3404.00.0011

Properties

- Broadband frequency range from DC to 3 GHz
- Space saving inline design
- DC continuity for remote powering
- Fix installed GDT, static spark over-voltage nom. 150 V



Product configuration	
Main path connectors	Port 1: unprotected, TNC jack (female) Port 2: protected, MMCX jack (female)
Mounting and grounding	MH119 (bulkhead mounting)
Side of bulkhead	protected side

Interface and material data	
Housing material / plating	Stainless Steel / Passivated (Plating)
Center contact, material / plating	Port 1: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)
	Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

Electrical data	
Impedance	50 Ω
Frequency frame	0 MHz to 3000 MHz
Return loss typical	≥ 20 dB
Insertion loss typical	≤ 0.25 dB
CW power frame	≤ 30 W
Static spark voltage	150 V, +/- 20 % (@ 100 V/s)
Residual pulse energy (typ.)	350 μJ (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Surge current handling capability	10 kA single, 5 kA multiple (test pulse 8/20 μs)

Electrical remarks	
DC supply voltage	28 V
DC current	2 A
Gas tube	Yes DC, GDT included, not replaceable

COAXIAL SURGE PROTECTOR DEVICE, Miniature GDT technology
3404.00.0011

Mechanical data	
Weight	36 g
Mating cycles	500
Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85°C
Ingress protection (IP Rating)	Unmated / IP68, according to IEC 60529 (30 min of water, 3 m)
Ingress protection (comment)	Waterproof TNC interface, even in un-mated conditions : IP68 acc. IEC 60529 and MIL-STD 810G Method 512.5, Procedure I
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. D
Moisture resistance according	MIL-STD-202, Method 106
Comment	
	Mounting hole: 5/8-24 UNEF-2B, (16.1 mm or MH119)

Ordering Information Table	
Item number	Item description
85155044	3404.00.0011

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1980 / Date of publication: 20.02.2024 / uncontrolled copy