



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Sealing Plug**

Cavity Diameter: **1.55 mm [.061 in]**

Primary Product Color: **Violet**

Primary Product Material: **PA GF**

Features

Product Type Features

Connector Seal & Plug Type	Sealing Plug
----------------------------	--------------

Body Features

Primary Product Color	Violet
Primary Product Material	PA GF

Dimensions

Wire Size	18 AWG
Cavity Diameter	1.55 mm[.061 in]

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted



	Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-2112780-0
TWO WHEELER



TE Part # 5-2112780-1
2W 18P ASSEMBLY REC WITH SEALED




TE Part # 1-2208720-1
105POS,MCON 1.2 CB,REC HSG, ASSY,SLD



TE Part # 3-2112780-1
18POS, MIXED,REC HSG,ASSY, SEALED

Also in the Series | MCON 1.2mm



Automotive Connector Locks & Position Assurance(9)




Automotive Housings(353)



Automotive Seals & Cavity Plugs(16)



Automotive Signal & Power Connector Housings(349)



Other Automotive Connector Accessories(12)

Customers Also Bought



TE Part #3-1418448-2
3POS MCP1.5k REC HSG CO MID
POS CLOSED



TE Part #6-1419167-1
2X8 MALE INLINE ASSY KEY A



TE Part #1564880-1
GET 0.64,FEMALE TERMINAL 0.13M



TE Part #2301462-1
30POS,HYBRID,REC HSG ASSY,SLD,
COD A




TE Part #2327375-1
26POS,MCON 1.2,REC HSG ASSY,SLD,
COD A




TE Part #2441242-1
66POS,HYBRID,REC HSG ASSY,
UNSLD,DOOR CON




TE Part #936098-1
090III 26P PLUG ASSY



TE Part #1-1579028-6
TUBE



TE Part #2498813-1
TAB CONN CVR,66POS,HYBRID,LH



TE Part #2498813-2
TAB CONN CVR,66POS,HYBRID,RH

Documents

Product Drawings
BLIND PLUG,MCON 1.2 CB
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2286476-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2286476-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2286476-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Data sheet

English

[product-2286476-1_datasheet](#)

English